



GreenUp deep recessed downlight G2

DN035B D150 LED20/865 PSU WH G2

GreenUp deep recessed downlight G2, 16.5 W, 2000 lm, 6500 K, Diffused lens optic, IP20 | Finger-protected

The GreenUp deep recessed downlight G2 line offers a selection of popular LED luminaires that not only capture the trend of deep recessed but also come with high levels of Philips quality at a competitive price. Reliable, energy-efficient and affordable—just what you need.

Product data

| General Information | | Number of products on MCB of 16 A type B | |
|------------------------------------|--------------|--|-------------------------|
| Light source engine type | LED | | 112 |
| Value ladder | Value | Protection class IEC | Safety class II |
| Light Technical | | Controls and Dimming | |
| Luminous Flux | 2,000 lm | Dimmable | No |
| Correlated Color Temperature (Nom) | 6500 K | Control interface | - |
| Luminous Efficacy (rated) (Nom) | 110 lm/W | Mechanical and Housing | |
| Color rendering index (CRI) | 80 | Housing Material | Plastic |
| Light source color | White | Optical cover material | Polycarbonate |
| Unified glare rating CEN | 28 | Housing Color | Black |
| Operating and Electrical | | Optical cover finish | Diffused lens optic |
| Input Voltage | 220 to 240 V | Ingress protection code | IP20 [Finger-protected] |
| Line Frequency | 50 or 60 Hz | Mech. impact protection code | IK03 [0.3 J] |
| Power Consumption | 16.5 W | Optical cover type | Polycarbonate Diffuser |
| Power Factor (Fraction) | 0.9 | Net Weight (Piece) | 0.220 kg |

GreenUp deep recessed downlight G2

Approval and Application

| | |
|---------------------------|---------------|
| CE mark | Yes |
| Ambient temperature range | -20 to +40 °C |

Initial Performance (IEC Compliant)

| | |
|-----------------------------|-------------|
| Luminous flux tolerance | -10% / +20% |
| Power consumption tolerance | +/-10% |

Product Data

| | |
|--------------------|---------------------------------|
| Order product name | DN035B D150 LED20/865 PSU WH G2 |
|--------------------|---------------------------------|

| | |
|---------------------------------|---------------------------------|
| Full product name | DN035B D150 LED20/865 PSU WH G2 |
| Full product code | 692382867616299 |
| Order code | 911401565043 |
| Material Nr. (12NC) | 911401565043 |
| Numerator - Quantity Per Pack | 1 |
| EAN/UPC - Product/Case | 6923828676162 |
| Numerator - Packs per outer box | 36 |
| EAN/UPC - Case | 6923828676384 |

Dimensional drawing

