



GreenUp deep recessed downlight G2

DN035B D200 LED32/830 PSU WH G2

GreenUp deep recessed downlight G2, 26 W, 2880 lm, 3000 K, Diffused lens optic, IP20 | Finger-protected

The GreenUp deep recessed downlight G2 line offers a selection of popular LED luminaires that not only capture the trend of deep recessed but also come with high levels of Philips quality at a competitive price. Reliable, energy-efficient and affordable—just what you need.

Product data

General Information		Number of products on MCB of 16 A type B	
Light source engine type	LED	135	
Value ladder	Value	Protection class IEC	Safety class II
Light Technical		Controls and Dimming	
Luminous Flux	2,880 lm	Dimmable	No
Correlated Color Temperature (Nom)	3000 K	Control interface	-
Luminous Efficacy (rated) (Nom)	99 lm/W	Mechanical and Housing	
Color rendering index (CRI)	80	Housing Material	Plastic
Light source color	White	Optical cover material	Polycarbonate
Unified glare rating CEN	28	Housing Color	Black
Operating and Electrical		Optical cover finish	Diffused lens optic
Input Voltage	220 to 240 V	Ingress protection code	IP20 [Finger-protected]
Line Frequency	50 or 60 Hz	Mech. impact protection code	IK03 [0.3 J]
Power Consumption	26 W	Optical cover type	Polycarbonate Diffuser
Power Factor (Fraction)	0.9	Net Weight (Piece)	0.402 kg

GreenUp deep recessed downlight G2

Approval and Application

CE mark	Yes
Ambient temperature range	-20 to +40 °C

Initial Performance (IEC Compliant)

Luminous flux tolerance	-10% / +20%
Power consumption tolerance	+/-10%

Product Data

Order product name	DN035B D200 LED32/830 PSU WH G2
--------------------	---------------------------------

Full product name	DN035B D200 LED32/830 PSU WH G2
Full product code	692382867620999
Order code	911401565443
Material Nr. (12NC)	911401565443
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	6923828676209
Numerator - Packs per outer box	18
EAN/UPC - Case	6923828676469

Dimensional drawing

