



# GreenPerform Troffer

## RC100X LED37S 840 W60L60 IAR G3

GreenPerform Troffer, 119 lm/W, 840 neutral white, InterAct Pro

GreenPerform troffer improves the compact design of the last generation with performance improvement and more variants for different markets. Integrating with all available system: POE, InterAct office wireless, InterAct Office Pro, ActiLume controller, GreenPerform troffer offers additional energy saving and connected features.

### Product data

General Information	
Light source replaceable	No
Number of gear units	1 unit
Driver included	Yes
Light source engine type	LED
Service tag	Yes
Value ladder	Performance
Warranty period	3 years

  

Light Technical	
Luminous Flux	3,700 lm
Correlated Color Temperature (Nom)	4000 K
Luminous Efficacy (rated) (Nom)	119 lm/W
Color rendering index (CRI)	80
Light source color	840 neutral white

  

Operating and Electrical	
Input Voltage	220 to 240 V
Line Frequency	50 to 60 Hz
Inrush current	22 A

Inrush time	270 ms
Power Consumption	31 W
Power Factor (Fraction)	0.95
Number of products on MCB of 16 A type B	22
Suitable for random switching	No
Protection class IEC	Safety class I

  

Controls and Dimming	
Dimmable	Yes
Control interface	InterAct Pro
Constant light output	No

  

Mechanical and Housing	
Housing Material	Metal
Optic material	Polycarbonate
Optical cover material	Polycarbonate
Fixation material	Steel
Housing Color	White
Optical cover finish	Ribbed
Overall length	597 mm

## GreenPerform Troffer

Overall width	597 mm
Overall height	46 mm
Dimensions (Height x Width x Depth)	46 x 597 x 597 mm
Ingress protection code	IP20 [Finger-protected]
Mech. impact protection code	IK03 [0.3 J]
Optical cover type	Variable linear-lens array in polycarbonate cover
Net Weight (Piece)	2.799 kg

### Approval and Application

Glow-wire test	Temperature 600 °C, duration 30 s
Flammability mark	For mounting on normally flammable surfaces
CE mark	Yes
Ambient temperature range	-20 to +40 °C

### Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-10%
-------------------------	--------

Initial chromaticity	SDCM<4
Power consumption tolerance	+/-10%

### Over Time Performance (IEC Compliant)

Median useful life L70B50	50,000 hour(s)
---------------------------	----------------

### Product Data

Order product name	RC100X LED37S 840 W60L60 IAR G3
Full product name	RC100X LED37S 840 W60L60 IAR G3
Full product code	911401568841
Order code	911401568841
Material Nr. (12NC)	911401568841
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	2

### Dimensional drawing

