



SlimBalance G3

RC570B LED50/9TW L150W6 SD PSD

SlimBalance G3, 126 lm/W, Tunable white, DALI

SlimBalance G3 SP570P is a flexible linear office offer which fits a variety of spaces like office, education. It offers flexible width of 35/60/90/120mm and length of 600/1200/1500mm to fit multiple applications. Geometric shapes help further create differentiated space. By means of its special designed structure, it offers quick and easy installation and maintenance. UGR19 is available for certain types through customized solution to provide a better visual comfort office environment.

Product data

General Information	
Light source engine type	LED
Service tag	Yes
Value ladder	Performance
Light Technical	
Luminous Flux	5,170 lm
Correlated Color Temperature (Nom)	Tunable White
Luminous Efficacy (rated) (Nom)	126 lm/W
Color rendering index (CRI)	>90
Beam angle of light source	116 degree(s)
Light source color	Tunable white
Unified glare rating CEN	27
Operating and Electrical	
Input Voltage	220-240 V
Line Frequency	50 or 60 Hz
Inrush current	29.6 A
Power Consumption	41 W

Power Factor (Fraction)	0.9
Number of products on MCB of 16 A type B	16
Protection class IEC	Safety class I
Controls and Dimming	
Dimmable	DALI
Control interface	DALI
Mechanical and Housing	
Housing Material	Aluminum Alloy
Optical cover material	Polycarbonate
Housing Color	White RAL 9003
Optical cover finish	Frosted
Overall length	1,530 mm
Overall width	70 mm
Overall height	80 mm
Dimensions (Height x Width x Depth)	80 x 70 x 1530 mm
Ingress protection code	IP20 [Finger-protected]
Mech. impact protection code	IK03 [0.3 J]

SlimBalance G3

Optical cover type	Polycarbonate bowl/cover frosted
Net Weight (Piece)	3.000 kg

Approval and Application

Glow-wire test	Temperature 650 °C, duration 30 s
Flammability mark	For mounting on normally flammable surfaces
CE mark	Yes
Performance ambient temperature Tq	25 °C
Ambient temperature range	-20 to +40 °C

Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-10%
-------------------------	--------

Initial chromaticity	SDCM<=4
Power consumption tolerance	+/-10%

Product Data

Order product name	RC570B LED50/9TW L150W6 SD PSD
Full product name	RC570B LED50/9TW L150W6 SD PSD
Order code	911401569342
Material Nr. (12NC)	911401569342
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	2

Dimensional drawing

