



GreenUp Track

ST306T P10 930 PSU WB BK SR

GreenUp Track, 10 W, 850 lm, 3000 K

Retail & Hospitality has a clear trend that clusters of choices is one of the most important DNAs that being strongly expected in this specific applications. GreenUp Track product family offers a complete track light solutions with aesthetic and compact product design, comprehensive control availability and specification options. It offers an outstanding color rendering performance and glare control effect, tailored for retail and hospitality applications.

Product data

General Information		Controls and Dimming	
Light source engine type	LED	Dimmable	No
Value ladder	Value	Control interface	-
Light Technical		Mechanical and Housing	
Luminous Flux	850 lm	Housing Material	Aluminum die cast
Correlated Color Temperature (Nom)	3000 K	Optical cover material	Polycarbonate
Luminous Efficacy (rated) (Nom)	85 lm/W	Housing Color	Black
Color rendering index (CRI)	>90	Optical cover finish	Smoke
Light source color	930 warm white	Overall length	150 mm
		Overall width	95 mm
		Overall height	185 mm
Operating and Electrical		Dimensions (Height x Width x Depth)	185 x 95 x 150 mm
Input Voltage	220-240 V	Ingress protection code	IP20 [Finger-protected]
Line Frequency	50 or 60 Hz	Mech. impact protection code	IK03 [0.3 J]
Power Consumption	10 W	Optical cover type	Lens
Power Factor (Fraction)	0.9	Net Weight (Piece)	1.035 kg
Number of products on MCB of 16 A type B	210		
Protection class IEC	Safety class II		

GreenUp Track

Approval and Application

CE mark	No
Ambient temperature range	-20 to +40 °C

Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-10%
Power consumption tolerance	+/-10%

Product Data

Order product name	ST306T P10 930 PSU WB BK SR
--------------------	-----------------------------

Full product name	ST306T P10 930 PSU WB BK SR
Full product code	872016952730099
Order code	911401569822
Material Nr. (12NC)	911401569822
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8720169527300
Numerator - Packs per outer box	12
EAN/UPC - Case	8720169538795

Dimensional drawing

