



GreenUp Track

ST306T P10 930 PSU WB BK SR

GreenUp Track, 10 W, 850 lm, 3000 K

Retail & Hospitality has a clear trend that clusters of choices is one of the most important DNAs that being strongly expected in this specific applications. GreenUp Track product family offers a complete track light solutions with aesthetic and compact product design, comprehensive control availability and specification options. It offers an outstanding color rendering performance and glare control effect, tailored for retail and hospitality applications.

Product data

General Information	
Light source engine type	LED
Value ladder	Value

Light Technical	
Luminous Flux	850 lm
Correlated Color Temperature (Nom)	3000 K
Luminous Efficacy (rated) (Nom)	85 lm/W
Color rendering index (CRI)	>90
Light source color	930 warm white

Operating and Electrical	
Input Voltage	220-240 V
Line Frequency	50 or 60 Hz
Power Consumption	10 W
Power Factor (Fraction)	0.9
Number of products on MCB of 16 A type B	210
Protection class IEC	Safety class II

Controls and Dimming	
Dimmable	No
Control interface	-

Mechanical and Housing	
Housing Material	Aluminum die cast
Optical cover material	Polycarbonate
Housing Color	Black
Optical cover finish	Smoke
Overall length	150 mm
Overall width	95 mm
Overall height	185 mm
Dimensions (Height x Width x Depth)	185 x 95 x 150 mm
Ingress protection code	IP20 [Finger-protected]
Mech. impact protection code	IK03 [0.3 J]
Optical cover type	Lens
Net Weight (Piece)	1.035 kg

GreenUp Track

Approval and Application

CE mark	No
Ambient temperature range	-20 to +40 °C

Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-10%
Power consumption tolerance	+/-10%

Product Data

Order product name	ST306T P10 930 PSU WB BK SR
--------------------	-----------------------------

Full product name	ST306T P10 930 PSU WB BK SR
Full product code	872016952730099
Order code	911401569822
Material Nr. (12NC)	911401569822
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8720169527300
Numerator - Packs per outer box	12
EAN/UPC - Case	8720169538795

Dimensional drawing

