



SlimBalance G3

RC570B End Cap W6 L60 PSD

Accessory, SlimBalance G3

SlimBalance G3 SP570P is a flexible linear office offer which fits a variety of spaces like office, education. It offers flexible width of 35/60/90/120mm and length of 600/1200/1500mm to fit multiple applications. Geometric shapes help further create differentiated space. By means of its special designed structure, it offers quick and easy installation and maintenance. UGR19 is available for certain types through customized solution to provide a better visual comfort office environment.

Product data

General Information	
Value ladder	Performance
Operating and Electrical	
Input Voltage	- V
Input Frequency	- Hz
Protection class IEC	-
Mechanical and Housing	
Overall length	75 mm
Overall width	80 mm
Overall height	82 mm
Dimensions (Height x Width x Depth)	82 x 80 x 75 mm
Material	Aluminum
Ingress protection code	-
Mech. impact protection code	-

Accessory color	White
Angle	-
Net Weight (Piece)	0.300 kg

Approval and Application	
CE mark	No

Product Data	
Order product name	RC570B End Cap W6 L60 PSD
Full product name	RC570B End Cap W6 L60 PSD
Order code	911401573242
Material Nr. (12NC)	911401573242
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	2

SlimBalance G3

Dimensional drawing

