



GreenSpace Accent Elbow GCGM

RS305B P6 930 PSD-E MB

GreenSpace Accent Elbow GCGM, 5.4 W, 6.6 W, 930 warm white, DALI, IP20 | Finger-protected

Retail & Hospitality has a clear trend that clusters of choices is one of the most important DNAs that being strongly expected in this specific applications. GreenSpace Accent Elbow is a product family with full choices in terms of optic choices, lumen diversities, control availability and wide range of tiltable angles, tailored for retail and hospitality applications.

Product data

| General Information | | Number of products on MCB of 16 A type B | |
|------------------------------------|----------------|--|-------------------------|
| Light source engine type | LED | | - |
| Value ladder | Performance | Protection class IEC | Safety class II |
| Light Technical | | Controls and Dimming | |
| Luminous Flux | 610 lm | Dimmable | Yes |
| Correlated Color Temperature (Nom) | 3000 K | Control interface | DALI |
| Luminous Efficacy (rated) (Nom) | 93 lm/W | Mechanical and Housing | |
| Color rendering index (CRI) | >90 | Housing Material | Aluminum Alloy |
| Light source color | 930 warm white | Optical cover material | Acrylate |
| Operating and Electrical | | Housing Color | White |
| Input Voltage | 200 to 240 V | Optical cover finish | Frosted |
| Line Frequency | 50 to 60 Hz | Ingress protection code | IP20 [Finger-protected] |
| Power Consumption | 5.4 6.6 W | Mech. impact protection code | IK03 [0.3 J] |
| Power Factor (Fraction) | 0.9 | Optical cover type | Acrylate |

GreenSpace Accent Elbow GCGM

| | |
|--------------------|----------|
| Net Weight (Piece) | 0.360 kg |
|--------------------|----------|

Approval and Application

| | |
|---------------------------|---------------|
| CE mark | No |
| Ambient temperature range | -20 to +40 °C |

Initial Performance (IEC Compliant)

| | |
|-----------------------------|--------|
| Luminous flux tolerance | +/-10% |
| Power consumption tolerance | +/-10% |

Product Data

| | |
|--------------------|------------------------|
| Order product name | RS305B P6 930 PSD-E MB |
|--------------------|------------------------|

| | |
|---------------------------------|------------------------|
| Full product name | RS305B P6 930 PSD-E MB |
| Full product code | 872016952847599 |
| Order code | 911401575302 |
| Material Nr. (12NC) | 911401575302 |
| Numerator - Quantity Per Pack | 1 |
| EAN/UPC - Product/Case | 8720169528475 |
| Numerator - Packs per outer box | 36 |
| EAN/UPC - Case | 8720169539969 |

Dimensional drawing

