



Truefashion Projector GCGM

ST700T LED30 930PW PSU MB 3C BK

Truefashion Projector GCGM, 35 W, PremiumWhite with CRI ≥ 90 and color temperature 3000K, IP20 | Finger-protected

Truefashion Projector is offering a retail segment with attractive outlook design, excellent quality of light & dedicated light recipe as well as system connectivity, to create a comfortable ambiance and impressive shopping experience to stimulate the store sales for retail customers.

Warnings and Safety

- 3 years

Product data

General Information		Operating and Electrical	
Light source engine type	-	Input Voltage	220 to 240 V
Service tag	Yes	Line Frequency	50 or 60 Hz
Value ladder	Specification	Power Consumption	35 W
Light Technical		Power Factor (Fraction)	0.9
Luminous Flux	3,294 lm	Number of products on MCB of 16 A type B	-
Correlated Color Temperature (Nom)	3000 K	Protection class IEC	Safety class II
Luminous Efficacy (rated) (Nom)	94 lm/W	Controls and Dimming	
Color rendering index (CRI)	>90	Dimmable	No
Light source color	PremiumWhite with CRI ≥ 90 and color temperature 3000K	Control interface	-
		Mechanical and Housing	
		Housing Material	Aluminum

Truefashion Projector GCGM

Optical cover material	Polymethyl methacrylate
Housing Color	White and black
Optical cover finish	Clear
Overall height	194 mm
Overall diameter	80 mm
Ingress protection code	IP20 [Finger-protected]
Mech. impact protection code	-
Optical cover type	Fashion proof optic beam angle 24°
Net Weight (Piece)	0.600 kg

Approval and Application

CE mark	Yes
Ambient temperature range	-20 to +35 °C

Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-10%
Power consumption tolerance	+/-10%

Product Data

Order product name	ST700T LED30 930PW PSU MB 3C BK
Full product name	ST700T LED30 930PW PSU MB 3C BK
Full product code	911401575561
Order code	911401575561
Material Nr. (12NC)	911401575561
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	1

Dimensional drawing

