Truefashion Projector GCGM

ST700T LED30 930PW PSD VLC WB BK

Truefashion Projector GCGM, 35 W, PremiumWhite with CRI ≥90 and color temperature 3000K, DALI, IP20 | Finger-protected

Truefashion Projector is offering a retail segment with attractive outlook design, excellent quality of light & dedicated light recipe as well as system connectivity, to create a comfortable ambiance and impressive shopping experience to stimulate the store sales for retail customers.

Warnings and Safety

- 3 years

Product data

General Information	
Light source engine type	-
Service tag	Yes
Value ladder	Specification

Light Technical	
Luminous Flux	3,168 lm
Correlated Color Temperature (Nom)	3000 K
Luminous Efficacy (rated) (Nom)	91 lm/W
Color rendering index (CRI)	>90
Light source color	PremiumWhite with CRI ≥90 and color temperature 3000K

Operating and Electrical	
Input Voltage	220 to 240 V
Line Frequency	50 or 60 Hz
Power Consumption	35 W
Power Factor (Fraction)	0.9
Number of products on MCB of 16 A type B	-
Protection class IEC	Safety class II

Controls and Dimming	
Dimmable	No
Control interface	DALI

Mechanical and Housing	
Housing Material	Aluminum

Truefashion Projector GCGM

Optical cover material	Polymethyl methacrylate
Housing Color	White and black
Optical cover finish	Clear
Overall height	194 mm
Overall diameter	80 mm
Ingress protection code	IP20 [Finger-protected]
Mech. impact protection code	-
Optical cover type	Fashion proof optic beam angle 36°
Net Weight (Piece)	0.900 kg

Approval and Application

CE mark	Yes
Ambient temperature range	-20 to +35 °C

Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-10%
Power consumption tolerance	+/-10%

Product Data

Order product name	ST700T LED30 930PW PSD VLC WB BK
Full product name	ST700T LED30 930PW PSD VLC WB BK
Full product code	911401576061
Order code	911401576061
Material Nr. (12NC)	911401576061
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	1

Dimensional drawing



© 2023 Signify Holding All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.