



GreenSpace Surface Mount

SM303C P9 927 PSU WB

GreenSpace Surface Mount, 8.1 W, 9.9 W, 770 lm, 2700 K, Frosted, IP20 | Finger-protected

Retail & Hospitality has a clear trend that clusters of choices is one of the most important DNAs that being strongly expected in this specific applications. GreenSpace Surface Mount is the entry level downlight family dedicated with suspension and surface mount versions, which offers a complete range of options for optical solutions, lumen outputs and color temperatures with multiple form factors available.

Product data

| General Information | | Controls and Dimming | |
|--|-----------------|------------------------------|-------------------------|
| Light source engine type | LED | Dimmable | No |
| Value ladder | Performance | Control interface | - |
| Light Technical | | Mechanical and Housing | |
| Luminous Flux | 770 lm | Housing Material | Aluminum Alloy |
| Correlated Color Temperature (Nom) | 2700 K | Optical cover material | Acrylate |
| Luminous Efficacy (rated) (Nom) | 85 lm/W | Housing Color | White |
| Color rendering index (CRI) | >90 | Optical cover finish | Frosted |
| Light source color | 927 warm white | Ingress protection code | IP20 [Finger-protected] |
| Operating and Electrical | | Mech. impact protection code | IK03 [0.3 J] |
| Input Voltage | 200 to 240 V | | |
| Line Frequency | 50 to 60 Hz | | |
| Power Consumption | 8.1 9.9 W | | |
| Power Factor (Fraction) | 0.5 | | |
| Number of products on MCB of 16 A type B | - | | |
| Protection class IEC | Safety class II | | |

GreenSpace Surface Mount

| | |
|--------------------|----------|
| Optical cover type | Acrylate |
| Net Weight (Piece) | 0.343 kg |

Approval and Application

| | |
|---------------------------|---------------|
| CE mark | No |
| Ambient temperature range | -20 to +40 °C |

Initial Performance (IEC Compliant)

| | |
|-----------------------------|--------|
| Luminous flux tolerance | +/-10% |
| Power consumption tolerance | +/-10% |

Product Data

| | |
|--------------------|----------------------|
| Order product name | SM303C P9 927 PSU WB |
|--------------------|----------------------|

| | |
|---------------------------------|----------------------|
| Full product name | SM303C P9 927 PSU WB |
| Full product code | 872016952681599 |
| Order code | 911401579012 |
| Material Nr. (12NC) | 911401579012 |
| Numerator - Quantity Per Pack | 1 |
| EAN/UPC - Product/Case | 8720169526815 |
| Numerator - Packs per outer box | 24 |
| EAN/UPC - Case | 8720169538306 |

Dimensional drawing

