GreenSpace Accent Elbow GCGM

RS305B P9 940 PSU-E VWB

GreenSpace Accent Elbow GCGM, 8.1 W, 9.9 W, 940 neutral white, IP20 | Finger-protected

Retail & Hospitality has a clear trend that clusters of choices is one of the most important DNAs that being strongly expected in this specific applications. GreenSpace Accent Elbow is a product family with full choices in terms of optic choices, lumen diversities, control availability and wide range of tiltable angles, tailored for retail and hospitality applications.

Product data

General Information	
Light source engine type	LED
Value ladder	Performance

Light Technical	
Luminous Flux	860 lm
Correlated Color Temperature (Nom)	4000 K
Luminous Efficacy (rated) (Nom)	96 lm/W
Color rendering index (CRI)	>90
Light source color	940 neutral white

Operating and Electrical	
Input Voltage	200 to 240 V
Line Frequency	50 to 60 Hz
Power Consumption	8.1 9.9 W
Power Factor (Fraction)	0.9
Number of products on MCB of 16 A type B	-
Protection class IEC	Safety class II

Controls and Dimming	
Dimmable	No
Control interface	-

Mechanical and Housing	
Housing Material	Aluminum Alloy
Optical cover material	Acrylate
Housing Color	White
Optical cover finish	Frosted
Ingress protection code	IP20 [Finger-protected]
Mech. impact protection code	IK03 [0.3 J]
Optical cover type	Acrylate

GreenSpace Accent Elbow GCGM

Net Weight (Piece)	0.345 kg

Approval and Application	
CE mark	No
Ambient temperature range	-20 to +40 °C

Initial Performance (IEC Compliant)	
Luminous flux tolerance	+/-10%
Power consumption tolerance	+/-10%

Product Data	
Order product name	RS305B P9 940 PSU-E VWB

Full product name	RS305B P9 940 PSU-E VWB
Full product code	872016952858199
Order code	911401580302
Material Nr. (12NC)	911401580302
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8720169528581
Numerator - Packs per outer box	36
EAN/UPC - Case	8720169540071

Dimensional drawing



© 2023 Signify Holding All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.