



GreenUp Track

ST306T P40 930 PSU WB BK SR

GreenUp Track, 40 W, 3720 lm, 3000 K

Retail & Hospitality has a clear trend that clusters of choices is one of the most important DNAs that being strongly expected in this specific applications. GreenUp Track product family offers a complete track light solutions with aesthetic and compact product design, comprehensive control availability and specification options. It offers an outstanding color rendering performance and glare control effect, tailored for retail and hospitality applications.

Product data

| General Information | | Controls and Dimming | |
|--|-----------------|-------------------------------------|-------------------------|
| Light source engine type | LED | Dimmable | No |
| Value ladder | Value | Control interface | - |
| Light Technical | | Mechanical and Housing | |
| Luminous Flux | 3,720 lm | Housing Material | Aluminum die cast |
| Correlated Color Temperature (Nom) | 3000 K | Optical cover material | Polycarbonate |
| Luminous Efficacy (rated) (Nom) | 93 lm/W | Housing Color | Black |
| Color rendering index (CRI) | >90 | Optical cover finish | Smoke |
| Light source color | 930 warm white | Overall length | 175 mm |
| Operating and Electrical | | Overall width | 115 mm |
| Input Voltage | 220-240 V | Overall height | 185 mm |
| Line Frequency | 50 or 60 Hz | Dimensions (Height x Width x Depth) | 185 x 115 x 175 mm |
| Power Consumption | 40 W | Ingress protection code | IP20 [Finger-protected] |
| Power Factor (Fraction) | 0.9 | Mech. impact protection code | IK03 [0.3 J] |
| Number of products on MCB of 16 A type B | 51 | Optical cover type | Lens |
| Protection class IEC | Safety class II | Net Weight (Piece) | 1.104 kg |

GreenUp Track

Approval and Application

| | |
|---------------------------|---------------|
| CE mark | No |
| Ambient temperature range | -20 to +40 °C |

Initial Performance (IEC Compliant)

| | |
|-----------------------------|--------|
| Luminous flux tolerance | +/-10% |
| Power consumption tolerance | +/-10% |

Product Data

| | |
|--------------------|-----------------------------|
| Order product name | ST306T P40 930 PSU WB BK SR |
|--------------------|-----------------------------|

| | |
|---------------------------------|-----------------------------|
| Full product name | ST306T P40 930 PSU WB BK SR |
| Full product code | 872016952516099 |
| Order code | 911401580622 |
| Material Nr. (12NC) | 911401580622 |
| Numerator - Quantity Per Pack | 1 |
| EAN/UPC - Product/Case | 8720169525160 |
| Numerator - Packs per outer box | 8 |
| EAN/UPC - Case | 8720169536654 |

Dimensional drawing

