



GreenUp Track

ST306T P40 940 PSU WB BK SR

GreenUp Track, 40 W, 3800 lm, 4000 K

Retail & Hospitality has a clear trend that clusters of choices is one of the most important DNAs that being strongly expected in this specific applications. GreenUp Track product family offers a complete track light solutions with aesthetic and compact product design, comprehensive control availability and specification options. It offers an outstanding color rendering performance and glare control effect, tailored for retail and hospitality applications.

Product data

General Information	
Light source engine type	LED
Value ladder	Value
Light Technical	
Luminous Flux	3,800 lm
Correlated Color Temperature (Nom)	4000 K
Luminous Efficacy (rated) (Nom)	95 lm/W
Color rendering index (CRI)	>90
Light source color	940 neutral white
Operating and Electrical	
Input Voltage	220-240 V
Line Frequency	50 or 60 Hz
Power Consumption	40 W
Power Factor (Fraction)	0.9
Number of products on MCB of 16 A type B	51
Protection class IEC	Safety class II

Controls and Dimming	
Dimmable	No
Control interface	-
Mechanical and Housing	
Housing Material	Aluminum die cast
Optical cover material	Polycarbonate
Housing Color	Black
Optical cover finish	Smoke
Overall length	175 mm
Overall width	115 mm
Overall height	185 mm
Dimensions (Height x Width x Depth)	185 x 115 x 175 mm
Ingress protection code	IP20 [Finger-protected]
Mech. impact protection code	IK03 [0.3 J]
Optical cover type	Lens
Net Weight (Piece)	1.104 kg

GreenUp Track

Approval and Application

CE mark	No
Ambient temperature range	-20 to +40 °C

Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-10%
Power consumption tolerance	+/-10%

Product Data

Order product name	ST306T P40 940 PSU WB BK SR
--------------------	-----------------------------

Full product name	ST306T P40 940 PSU WB BK SR
Full product code	872016952860499
Order code	911401580922
Material Nr. (12NC)	911401580922
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8720169528604
Numerator - Packs per outer box	8
EAN/UPC - Case	8720169540095

Dimensional drawing

