



GreenSpace Surface Mount

SM303C P6S 927 PSU MB

GreenSpace Surface Mount, 5.4 W, 6.6 W, 500 lm, 2700 K, Frosted, IP20 | Finger-protected

Retail & Hospitality has a clear trend that clusters of choices is one of the most important DNAs that being strongly expected in this specific applications. GreenSpace Surface Mount is the entry level downlight family dedicated with suspension and surface mount versions, which offers a complete range of options for optical solutions, lumen outputs and color temperatures with multiple form factors available.

Product data

General Information		Power Factor (Fraction)		0.5
Light source engine type	LED	Number of products on MCB of 16 A type B		-
Value ladder	Performance	Protection class IEC		Safety class II
Light Technical		Controls and Dimming		
Luminous Flux	500 lm	Dimmable	No	
Correlated Color Temperature (Nom)	2700 K	Control interface	-	
Luminous Efficacy (rated) (Nom)	84 lm/W	Mechanical and Housing		
Color rendering index (CRI)	>90	Housing Material	Aluminum Alloy	
Light source color	927 warm white	Optical cover material	Acrylate	
Operating and Electrical		Housing Color	White	
Input Voltage	200 to 240 V	Optical cover finish	Frosted	
Line Frequency	50 to 60 Hz	Ingress protection code	IP20 [Finger-protected]	
Power Consumption	5.4 6.6 W	Mech. impact protection code	IK03 [0.3 J]	

GreenSpace Surface Mount

Optical cover type	Acrylate
Net Weight (Piece)	0.391 kg

Approval and Application

CE mark	No
Ambient temperature range	-20 to +40 °C

Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-10%
Power consumption tolerance	+/-10%

Product Data

Order product name	SM303C P6S 927 PSU MB
--------------------	-----------------------

Full product name	SM303C P6S 927 PSU MB
Full product code	872016952519199
Order code	911401582912
Material Nr. (12NC)	911401582912
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8720169525191
Numerator - Packs per outer box	24
EAN/UPC - Case	8720169536685

Dimensional drawing

