



GreenSpace Flex Luna

RS378B P12 930 PSD MB D100 M-WH PROCAU

GreenSpace Flex Luna, 12.8 W, 930 warm white, DALI, IP20 | Finger-protected

Ever-changing yet dependable, the moon reflects the very essence of hospitality lighting, which is adaptable, elegant, and always in tune with its surroundings. GreenSpace Flex Luna is designed to evoke a unique sensation. Like the moon, Luna does not overpower but enhances its surroundings, casting a glow that feels both intimate and grand. It is not just a light. It is an intimate experience.

Product data

General Information		Number of products on MCB of 16 A type B 85	
Driver included	Yes	Protection class IEC	Safety class II
Light source engine type	LED	Controls and Dimming	
Value ladder	Performance	Dimmable	DALI
Light Technical		Control interface	DALI
Luminous Flux	1,510 lm	Mechanical and Housing	
Correlated Color Temperature (Nom)	3000 K	Housing Material	Aluminum Alloy
Luminous Efficacy (rated) (Nom)	118 lm/W	Optical cover material	Polycarbonate
Color rendering index (CRI)	92	Housing Color	Black
Light source color	930 warm white	Optical cover finish	Structured optic
Unified glare rating CEN	16	Ingress protection code	IP20 [Finger-protected]
Operating and Electrical		Mech. impact protection code	IK03 [0.35 J reinforced]
Input Voltage	220 to 240 V	Optical cover type	Lens
Line Frequency	50 or 60 Hz	Net Weight (Piece)	0.780 kg
Power Consumption	12.8 W		
Power Factor (Fraction)	0.9		

GreenSpace Flex Luna

Approval and Application

CE mark	No
ENEC mark	-
Ambient temperature range	-20 to +45 °C

Initial Performance (IEC Compliant)

Luminous flux tolerance	-10% / +10%
Power consumption tolerance	+/-10%

Product Data

Order product name	RS378B P12 930 PSD MB D100 M-WH PROCAU
--------------------	---

Full product name	RS378B P12 930 PSD MB D100 M-WH PROCAU
Order code	911401583247
Material Nr. (12NC)	911401583247
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	18

Dimensional drawing

