PHILIPS

Lighting

Aura

RC430X LED35/9TW W60L60 SC15 OC

Aura, 118 lm/W, Tunable white, InterAct office

As an innovative troffer, CoreView Pro RC430V uses indirect and direct light output to reach UGR19 without using heavy and big glare control plates. The central module can be easily replaceable for future maintenance. The light from the central light module can be controlled separately to fit multiple applications. BioUp technology provides better well being for the people in indoor environment.

Product data

General Information	
Number of gear units	1 unit
Gear	-
Driver included	Yes
Light source engine type	LED
Value ladder	Specification
Warranty period	3 years

Light Technical	
Luminous Flux	3,500 lm
Correlated Color Temperature (Nom)	Tunable white 2700-6500 K
Luminous Efficacy (rated) (Nom)	118 lm/W
Color rendering index (CRI)	90
Number of light sources	1
Beam angle of light source	115 degree(s)
Light source color	Tunable white
Optic type	Beam angle 90°
Luminaire light beam spread	90°
Unified glare rating CEN	19

Operating and Electrical	
Input Voltage	220-240 V
Line Frequency	50 or 60 Hz
Inrush current	6.26 A
Inrush time	0.035 ms
Power Consumption	29 W
Power Factor (Fraction)	0.9
Connection	-
Cable	-
Number of products on MCB of 16 A type B	53
Suitable for random switching	Yes
Protection class IEC	Safety class II

Controls and Dimming	
Dimmable	Wireless Dim
Control interface	InterAct office
Maximum dim level	1%

Mechanical and Housing	
Housing Material	Metal

Aura

Reflector material	Steel
Optic material	Polycarbonate
Optical cover material	Polystyrene
Housing Color	White RAL 9003
Mounting device	Recessed mounting box square
Optical cover finish	Diffused lens optic
Overall length	595 mm
Overall width	595 mm
Overall height	92 mm
Dimensions (Height x Width x Depth)	92 x 595 x 595 mm
Ingress protection code	IP20 [Finger-protected]
Mech. impact protection code	IK03 [0.3 J]
Optical cover type	Prismatic bowl/cover linear horizontal
Net Weight (Piece)	1.840 kg

Approval and Application

Glow-wire test	Temperature 650 °C, duration 30 s
Flammability mark	For mounting on normally flammable surfaces
CE mark	Yes
ENEC mark	ENEC mark

Photobiological risk	Photobiological risk group 0 @200mm to EN62778
EU RoHS compliant	Yes
Performance ambient temperature Tq	25 °C
Ambient temperature range	-20 to +40 °C

Initial Performance (IEC Compliant)

Luminous flux tolerance	-10% / +10%
Initial chromaticity	3
Power consumption tolerance	+/-10%

Product Data

Order product name	RC430X LED35/9TW W60L60 SC15 OC
Full product name	RC430X LED35/9TW W60L60 SC15 OC
Order code	911401583345
Material Nr. (12NC)	911401583345
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	2

Dimensional drawing



© 2025 Signify Holding All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.