



# Flex Cove G6

## LS165S COB 6W CRI90 3000K IP20 5M

Flex Cove G6, 420 lm, 70 lm/W, 930 warm white, 24 DC V, IP20 | Finger-protected

Philips Flex Cove G6 is the latest generation of our popular LED cove lighting. This comprehensive new family of flexible strip lights are designed to follow straight lines or curves to create beautiful ambiances that highlight architectural details. Both SPEC fighter and COST fighter are available within the family. As customizable cove lighting strips, SPEC fighter range also promise excellent energy-saving performance, superb lighting uniformity, and color consistency. All with a long lifetime that promises less lumen decay or color shifts. So with Flex Cove G6, you can flex your accent lighting to suit the requirements of any project - beautifully.

### Product data

General Information		Optic type	
Number of gear units	-	Optic type	-
Gear	-	Luminaire light beam spread	-
Driver included	No	Unified glare rating CEN	Not applicable
Light source engine type	LED	Operating and Electrical	
Warranty period	3 years	Input Voltage	24 DC V
Light Technical		Line Frequency	- Hz
Luminous Flux	420 lm	Power Consumption	29 W
Correlated Color Temperature (Nom)	3000 K	Power Factor (Fraction)	-
Luminous Efficacy (rated)	70 lm/W	Connection	-
Color rendering index (CRI)	90	Cable	-
Number of light sources	324	Number of products on MCB of 16 A type B	-
Beam angle of light source	140 degree(s)	Suitable for random switching	No
Light source color	930 warm white	Protection class IEC	Safety class III

# Flex Cove G6

## Controls and Dimming

Dimmable	1-10V DALI Fixed
Control interface	-
Maximum dim level	Not applicable

## Mechanical and Housing

Housing Material	Polycarbonate
Reflector material	-
Optic material	-
Optical cover material	-
Housing Color	-
Mounting device	-
Optical cover finish	-
Overall length	5,000 mm
Overall width	8 mm
Overall height	1.8 mm
Dimensions (Height x Width x Depth)	2 x 8 x 5000 mm
Ingress protection code	IP20 [Finger-protected]
Mech. impact protection code	-
Optical cover type	-
Net Weight (Piece)	0.070 kg

## Approval and Application

Glow-wire test	-
Flammability mark	-

CE mark	No
ENEC mark	-
Photobiological risk	Photobiological risk group 0 @200mm to EN62778
EU RoHS compliant	Yes
Performance ambient temperature Tq	25 °C
Ambient temperature range	-20 to +45 °C

## Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-10%
Initial chromaticity	(0.440,0.403) SDCM<=5
Power consumption tolerance	+/-10%

## Product Data

Order product name	LS165S COB 6W CRI90 3000K IP20 5M
Full product name	LS165S COB 6W CRI90 3000K IP20 5M
Full product code	692382864443799
Order code	911401583347
Material Nr. (12NC)	911401583347
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	6923828644437
Numerator - Packs per outer box	40
EAN/UPC - Case	6923828644529

## Dimensional drawing

