



GreenPerform Batten G3 BN398C

BN398C LED40/NW L1200 PSU OP

GreenPerform Batten G3 BN398C, 29 W, 4100 lm, 4000 K

GreenPerform batten BN398C is a cost competitive linear solution with good performance and multiple lumen output for retail and industry applications. It offers surface mount and suspension installations to cater for different mounting options. Its multiple optic designs accommodate different applications as well.

Product data

General Information		Protection class IEC		Safety class I	
Light source engine type	LED				
Value ladder	Performance				
Controls and Dimming					
Dimmable				No	
Control interface				-	
Mechanical and Housing					
Housing Material				Metal-Plastic	
Optical cover material				Polymethyl methacrylate	
Housing Color				White RAL 9003	
Optical cover finish				Frosted	
Overall length				1,135 mm	
Overall width				58 mm	
Overall height				58 mm	
Dimensions (Height x Width x Depth)				58 x 58 x 1135 mm	
Ingress protection code				IP20 [Finger-protected]	
Mech. impact protection code				IK03 [0.35 J reinforced]	
Optical cover type				Polymethyl methacrylate bowl/cover	

General Information	
Light source engine type	LED
Value ladder	Performance
Light Technical	
Luminous Flux	4,100 lm
Correlated Color Temperature (Nom)	4000 K
Luminous Efficacy (rated) (Nom)	141 lm/W
Color rendering index (CRI)	>80
Light source color	840 neutral white
Operating and Electrical	
Input Voltage	220-240 V
Line Frequency	50 or 60 Hz
Inrush current	6 A
Power Consumption	29 W
Power Factor (Fraction)	0.9
Number of products on MCB of 16 A type B	40

GreenPerform Batten G3 BN398C

Net Weight (Piece)	1.700 kg
Approval and Application	
Flammability mark	For mounting on normally flammable surfaces
CE mark	Yes
Ambient temperature range	-20 to +40 °C
Initial Performance (IEC Compliant)	
Luminous flux tolerance	+/-10%
Initial chromaticity	SDCM<5
Power consumption tolerance	+/-10%

Product Data	
Order product name	BN398C LED40/NW L1200 PSU OP
Full product name	BN398C LED40/NW L1200 PSU OP
Full product code	692382863343100
Order code	911401583451
Material Nr. (12NC)	911401583451
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	1

Dimensional drawing

