



# GreenSpace Surface Mount

## SM303C P6S 930 PSU VWB

GreenSpace Surface Mount, 5.4 W, 6.6 W, 520 lm, 3000 K, Frosted, IP20 | Finger-protected

Retail & Hospitality has a clear trend that clusters of choices is one of the most important DNAs that being strongly expected in this specific applications. GreenSpace Surface Mount is the entry level downlight family dedicated with suspension and surface mount versions, which offers a complete range of options for optical solutions, lumen outputs and color temperatures with multiple form factors available.

### Product data

General Information		Controls and Dimming	
Light source engine type	LED	Dimmable	No
Value ladder	Performance	Control interface	-
Light Technical		Mechanical and Housing	
Luminous Flux	520 lm	Housing Material	Aluminum Alloy
Correlated Color Temperature (Nom)	3000 K	Optical cover material	Acrylate
Luminous Efficacy (rated) (Nom)	87 lm/W	Housing Color	White
Color rendering index (CRI)	>90	Optical cover finish	Frosted
Light source color	930 warm white	Ingress protection code	IP20 [Finger-protected]
Operating and Electrical		Mech. impact protection code	IK03 [0.3 J]
Input Voltage	200 to 240 V	Power Factor (Fraction)	0.5
Line Frequency	50 to 60 Hz	Number of products on MCB of 16 A type B	-
Power Consumption	5.4 6.6 W	Protection class IEC	Safety class II

## GreenSpace Surface Mount

Optical cover type	Acrylate
Net Weight (Piece)	0.391 kg

### Approval and Application

CE mark	No
Ambient temperature range	-20 to +40 °C

### Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-10%
Power consumption tolerance	+/-10%

### Product Data

Order product name	SM303C P6S 930 PSU VWB
--------------------	------------------------

Full product name	SM303C P6S 930 PSU VWB
Full product code	872016952437899
Order code	911401583512
Material Nr. (12NC)	911401583512
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8720169524378
Numerator - Packs per outer box	24
EAN/UPC - Case	8720169535862

## Dimensional drawing

