



GreenPerform Batten G3 BN398C

BN398C LED69/NW L1200 PSU OP

GreenPerform Batten G3 BN398C, 49 W, 6900 lm, 4000 K

GreenPerform batten BN398C is a cost competitive linear solution with good performance and multiple lumen output for retail and industry applications. It offers surface mount and suspension installations to cater for different mounting options. Its multiple optic designs accommodate different applications as well.

Product data

General Information		Protection class IEC		Safety class I	
Light source engine type	LED				
Value ladder	Performance				
Controls and Dimming					
Dimmable				No	
Control interface				-	
Mechanical and Housing					
Housing Material				Metal-Plastic	
Optical cover material				Polymethyl methacrylate	
Housing Color				White RAL 9003	
Optical cover finish				Frosted	
Overall length				1,135 mm	
Overall width				58 mm	
Overall height				58 mm	
Dimensions (Height x Width x Depth)				58 x 58 x 1135 mm	
Ingress protection code				IP20 [Finger-protected]	
Mech. impact protection code				IK03 [0.35 J reinforced]	
Optical cover type				Polymethyl methacrylate bowl/cover	

GreenPerform Batten G3 BN398C

Net Weight (Piece)	1.699 kg
Approval and Application	
Flammability mark	For mounting on normally flammable surfaces
CE mark	Yes
Ambient temperature range	-20 to +40 °C
Initial Performance (IEC Compliant)	
Luminous flux tolerance	+/-10%
Initial chromaticity	SDCM<5
Power consumption tolerance	+/-10%

Product Data	
Order product name	BN398C LED69/NW L1200 PSU OP
Full product name	BN398C LED69/NW L1200 PSU OP
Full product code	692382863341700
Order code	911401583651
Material Nr. (12NC)	911401583651
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	6923828633417
Numerator - Packs per outer box	1
EAN/UPC - Case	6923828633417

Dimensional drawing

