



GreenPerform Batten G3 BN398C

BN398C LED20/NW L600 PSD OP

GreenPerform Batten G3 BN398C, 14.5 W, 2100 lm, 4000 K, DALI

GreenPerform batten BN398C is a cost competitive linear solution with good performance and multiple lumen output for retail and industry applications. It offers surface mount and suspension installations to cater for different mounting options. Its multiple optic designs accommodate different applications as well.

Product data

General Information		Number of products on MCB of 16 A type B 38	
Light source engine type	LED	Protection class IEC	Safety class I
Value ladder	Performance		
Light Technical		Controls and Dimming	
Luminous Flux	2,100 lm	Dimmable	Yes
Correlated Color Temperature (Nom)	4000 K	Control interface	DALI
Luminous Efficacy (rated) (Nom)	144 lm/W		
Color rendering index (CRI)	>80	Mechanical and Housing	
Light source color	840 neutral white	Housing Material	Metal-Plastic
		Optical cover material	Polymethyl methacrylate
		Housing Color	White RAL 9003
		Optical cover finish	Frosted
Operating and Electrical		Overall length	573 mm
Input Voltage	220-240 V	Overall width	58 mm
Line Frequency	50 or 60 Hz	Overall height	58 mm
Inrush current	14.7 A	Dimensions (Height x Width x Depth)	58 x 58 x 573 mm
Power Consumption	14.5 W	Ingress protection code	IP20 [Finger-protected]
Power Factor (Fraction)	0.9		

GreenPerform Batten G3 BN398C

Mech. impact protection code	IK03 [0.35 J reinforced]
Optical cover type	Polymethyl methacrylate bowl/cover
Net Weight (Piece)	0.999 kg

Approval and Application

Flammability mark	For mounting on normally flammable surfaces
CE mark	Yes
Ambient temperature range	-20 to +40 °C

Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-10%
Initial chromaticity	SDCM<5
Power consumption tolerance	+/-10%

Product Data

Order product name	BN398C LED20/NW L600 PSD OP
Full product name	BN398C LED20/NW L600 PSD OP
Full product code	692382863337000
Order code	911401584051
Material Nr. (12NC)	911401584051
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	6923828633370
Numerator - Packs per outer box	1
EAN/UPC - Case	6923828633370

Dimensional drawing

