



GreenUp Linear

SM308C P22/840 L75W3 PSU MB WH

GreenUp Linear, 22 W, 2150 lm, 4000 K, Frosted, IP20 | Finger-protected

Retail & Hospitality has a clear trend that clusters of choices is one of the most important DNAs that being strongly expected in this specific applications. GreenUp Linear is the entry level linear product family, which offers the basic functional lighting performance, with multiple choices of installations, lumen outputs and product dimensions.

Product data

General Information		Protection class IEC	
Light source engine type	LED		Safety class II
Value ladder	Value		
Light Technical		Controls and Dimming	
Luminous Flux	2,150 lm	Dimmable	No
Correlated Color Temperature (Nom)	4000 K	Control interface	-
Luminous Efficacy (rated) (Nom)	98 lm/W	Mechanical and Housing	
Color rendering index (CRI)	>80	Housing Material	Aluminum extruded
Light source color	840 neutral white	Optical cover material	Polycarbonate
Operating and Electrical		Housing Color	White RAL 9003
Input Voltage	220-240 V	Optical cover finish	Frosted
Line Frequency	50 or 60 Hz	Ingress protection code	IP20 [Finger-protected]
Power Consumption	22 W	Mech. impact protection code	IK03 [0.3 J]
Power Factor (Fraction)	0.9	Optical cover type	Polycarbonate Diffuser
Number of products on MCB of 16 A type B	95	Net Weight (Piece)	0.830 kg
		Approval and Application	
		CE mark	No

GreenUp Linear

Ambient temperature range	+20 to +40 °C
Initial Performance (IEC Compliant)	
Luminous flux tolerance	+/-10%
Power consumption tolerance	+/-10%
Product Data	
Order product name	SM308C P22/840 L75W3 PSU MB WH
Full product name	SM308C P22/840 L75W3 PSU MB WH

Full product code	872016952524599
Order code	52524599
Material Nr. (12NC)	911401584222
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8720169525245
Numerator - Packs per outer box	10
EAN/UPC - Case	8720169536739

Dimensional drawing

