



# GreenUp Linear

## SM308C P22/865 L75W3 PSU WB WH

GreenUp Linear, 22 W, 2150 lm, 6500 K, Frosted, IP20 | Finger-protected

Retail & Hospitality has a clear trend that clusters of choices is one of the most important DNAs that being strongly expected in this specific applications. GreenUp Linear is the entry level linear product family, which offers the basic functional lighting performance, with multiple choices of installations, lumen outputs and product dimensions.

### Product data

General Information		Protection class IEC	
Light source engine type	LED	Safety class II	
Value ladder	Value	Controls and Dimming	
<b>Light Technical</b>		Dimmable	No
Luminous Flux	2,150 lm	Control interface	-
Correlated Color Temperature (Nom)	6500 K	Mechanical and Housing	
Luminous Efficacy (rated) (Nom)	98 lm/W	Housing Material	Aluminum extruded
Color rendering index (CRI)	>80	Optical cover material	Polycarbonate
Light source color	865 cool daylight	Housing Color	White RAL 9003
<b>Operating and Electrical</b>		Optical cover finish	Frosted
Input Voltage	220-240 V	Ingress protection code	IP20 [Finger-protected]
Line Frequency	50 or 60 Hz	Mech. impact protection code	IK03 [0.3 J]
Power Consumption	22 W	Optical cover type	Polycarbonate Diffuser
Power Factor (Fraction)	0.9	Net Weight (Piece)	0.830 kg
Number of products on MCB of 16 A type B	95	Approval and Application	
		CE mark	No

## GreenUp Linear

Ambient temperature range	+20 to +40 °C
<b>Initial Performance (IEC Compliant)</b>	
Luminous flux tolerance	+/-10%
Power consumption tolerance	+/-10%
<b>Product Data</b>	
Order product name	SM308C P22/865 L75W3 PSU WB WH
Full product name	SM308C P22/865 L75W3 PSU WB WH

Full product code	872016952869799
Order code	911401584522
Material Nr. (12NC)	911401584522
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8720169528697
Numerator - Packs per outer box	10
EAN/UPC - Case	8720169540187

### Dimensional drawing

