



# GreenSpace Surface Mount

## SM303C P6S 950 PSU VWB

GreenSpace Surface Mount, 5.4 W, 6.6 W, 560 lm, 5000 K, Frosted, IP20 | Finger-protected

Retail & Hospitality has a clear trend that clusters of choices is one of the most important DNAs that being strongly expected in this specific applications. GreenSpace Surface Mount is the entry level downlight family dedicated with suspension and surface mount versions, which offers a complete range of options for optical solutions, lumen outputs and color temperatures with multiple form factors available.

### Product data

General Information		Power Factor (Fraction)	
Light source engine type	LED		0.5
Value ladder	Performance	Number of products on MCB of 16 A type B	-
		Protection class IEC	Safety class II
Light Technical		Controls and Dimming	
Luminous Flux	560 lm	Dimmable	No
Correlated Color Temperature (Nom)	5000 K	Control interface	-
Luminous Efficacy (rated) (Nom)	93 lm/W		
Color rendering index (CRI)	>90	Mechanical and Housing	
Light source color	White	Housing Material	Aluminum Alloy
		Optical cover material	Acrylate
Operating and Electrical		Housing Color	White
Input Voltage	200 to 240 V	Optical cover finish	Frosted
Line Frequency	50 to 60 Hz	Ingress protection code	IP20 [Finger-protected]
Power Consumption	5.4 6.6 W	Mech. impact protection code	IK03 [0.3 J]

## GreenSpace Surface Mount

Optical cover type	Acrylate
Net Weight (Piece)	0.391 kg

### Approval and Application

CE mark	No
Ambient temperature range	-20 to +40 °C

### Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-10%
Power consumption tolerance	+/-10%

### Product Data

Order product name	SM303C P6S 950 PSU VWB
--------------------	------------------------

Full product name	SM303C P6S 950 PSU VWB
Full product code	872016952525299
Order code	911401584712
Material Nr. (12NC)	911401584712
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8720169525252
Numerator - Packs per outer box	24
EAN/UPC - Case	8720169536746

## Dimensional drawing

