



# GreenPerform Batten G3 BN398C

## BN398C LED87/CW L1500 PSU DA

GreenPerform Batten G3 BN398C, 68 W, 8500 lm, 6500 K

GreenPerform batten BN398C is a cost competitive linear solution with good performance and multiple lumen output for retail and industry applications. It offers surface mount and suspension installations to cater for different mounting options. Its multiple optic designs accommodate different applications as well.

### Product data

General Information		Protection class IEC	
Light source engine type	LED		Safety class I
Value ladder	Performance		
Light Technical		Controls and Dimming	
Luminous Flux	8,500 lm	Dimmable	No
Correlated Color Temperature (Nom)	6500 K	Control interface	-
Luminous Efficacy (rated) (Nom)	125 lm/W	Mechanical and Housing	
Color rendering index (CRI)	>80	Housing Material	Metal-Plastic
Light source color	865 cool daylight	Optical cover material	Polymethyl methacrylate
Operating and Electrical		Housing Color	White RAL 9003
Input Voltage	220-240 V	Optical cover finish	Clear
Line Frequency	50 or 60 Hz	Overall length	1,416 mm
Inrush current	19 A	Overall width	58 mm
Power Consumption	68 W	Overall height	58 mm
Power Factor (Fraction)	0.9	Dimensions (Height x Width x Depth)	58 x 58 x 1416 mm
Number of products on MCB of 16 A type B	24	Ingress protection code	IP20 [Finger-protected]
		Mech. impact protection code	IK03 [0.35 J reinforced]
		Optical cover type	Polymethyl methacrylate bowl/cover

# GreenPerform Batten G3 BN398C

Net Weight (Piece)	1.999 kg
<b>Approval and Application</b>	
Flammability mark	For mounting on normally flammable surfaces
CE mark	Yes
Ambient temperature range	-20 to +40 °C
<b>Initial Performance (IEC Compliant)</b>	
Luminous flux tolerance	+/-10%
Initial chromaticity	SDCM<5
Power consumption tolerance	+/-10%

<b>Product Data</b>	
Order product name	BN398C LED87/CW L1500 PSU DA
Full product name	BN398C LED87/CW L1500 PSU DA
Full product code	692382863322600
Order code	911401585551
Material Nr. (12NC)	911401585551
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	6923828633226
Numerator - Packs per outer box	1
EAN/UPC - Case	6923828633226

## Dimensional drawing

