GreenPerform Batten G3 BN398C

BN398C LED20/NW L600 PSU WB

GreenPerform Batten G3 BN398C, 15.5 W, 2000 lm, 4000 K

GreenPerform batten BN398C is a cost competitive linear solution with good performance and multiple lumen output for retail and industry applications. It offers surface mount and suspension installations to cater for different mounting options. Its multiple optic designs accommodate different applications as well.

Product data

General Information	
Light source engine type	LED
Value ladder	Performance

Light Technical	
Luminous Flux	2,000 lm
Correlated Color Temperature (Nom)	4000 K
Luminous Efficacy (rated) (Nom)	129 lm/W
Color rendering index (CRI)	>80
Light source color	840 neutral white

Operating and Electrical	
Input Voltage	220-240 V
Line Frequency	50 or 60 Hz
Inrush current	14 A
Power Consumption	15.5 W
Power Factor (Fraction)	0.9
Number of products on MCB of 16 A type B	33

Protection class IEC	Safety class I

Controls and Dimming	
Dimmable	No
Control interface	-

Mechanical and Housing	
Housing Material	Metal–Plastic
Optical cover material	Polymethyl methacrylate
Housing Color	White RAL 9003
Optical cover finish	Clear
Overall length	573 mm
Overall width	58 mm
Overall height	58 mm
Dimensions (Height x Width x Depth)	58 x 58 x 573 mm
Ingress protection code	IP20 [Finger-protected]
Mech. impact protection code	IK03 [0.35 J reinforced]
Optical cover type	Polymethyl methacrylate bowl/cover

GreenPerform Batten G3 BN398C

Net Weight (Piece)	0.999 kg

Approval and Application

Flammability mark	For mounting on normally flammable surfaces
CE mark	Yes
Ambient temperature range	-20 to +40 °C

Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-10%
Initial chromaticity	SDCM<5
Power consumption tolerance	+/-10%

Product Data

Order product name	BN398C LED20/NW L600 PSU WB
Full product name	BN398C LED20/NW L600 PSU WB
Full product code	692382863321900
Order code	911401585651
Material Nr. (12NC)	911401585651
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	6923828633219
Numerator - Packs per outer box	1
EAN/UPC - Case	6923828633219

Dimensional drawing



© 2023 Signify Holding All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.