



GreenPerform Panel RC099V G3

RC099V G3 LED37/850 PSU W60L60 OC

GreenPerform Panel RC099V G3, 110 lm/W, 850 neutral white

GreenPerform panel RC099V G3 is an affordable LED panel delivering comfortable light with excellent uniformity. It offers 3 types, 600x600, 300x1200, and 600x1200mm with max: 140lm/w. Its UGR19 brings more visual comfort in the office. Equipped with Dali, Interact and EcoSet, RC099V G2 offers easy connection to control system to bring better energy saving.

Product data

General Information		Number of products on MCB of 16 A type B	
Light source engine type	LED	17	
Service tag	Yes	Protection class IEC	Safety class II
Value ladder	Performance		
Light Technical		Controls and Dimming	
Luminous Flux	3,600 lm	Dimmable	No
Correlated Color Temperature (Nom)	5000 K	Control interface	-
Luminous Efficacy (rated) (Nom)	110 lm/W		
Color rendering index (CRI)	>80	Mechanical and Housing	
Light source color	850 neutral white	Housing Material	Metal
Operating and Electrical		Optical cover material	Polystyrene
Input Voltage	220-240 V	Housing Color	White RAL 9003
Line Frequency	50 or 60 Hz	Optical cover finish	Opal
Power Consumption	32.7 W	Ingress protection code	IP20 [Finger-protected]
Power Factor (Fraction)	0.9	Mech. impact protection code	IK03 [0.3 J]
		Optical cover type	Opal
		Net Weight (Piece)	1.800 kg

GreenPerform Panel RC099V G3

Approval and Application

CE mark	Yes
Ambient temperature range	-20 °C to 45 °C

Initial Performance (IEC Compliant)

Luminous flux tolerance	-10% / +10%
Power consumption tolerance	+/-10%

Product Data

Order product name	RC099V G3 LED37/850 PSU W60L60 OC
--------------------	-----------------------------------

Full product name	RC099V G3 LED37/850 PSU W60L60 OC
Order code	911401585842
Material Nr. (12NC)	911401585842
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	4

