



GreenPerform Panel RC099V G3

RC099V G3 LED37/840 PSU W60L60 OC

GreenPerform Panel RC099V G3, 110 lm/W, 840 neutral white

GreenPerform panel RC099V G3 is an affordable LED panel delivering comfortable light with excellent uniformity. It offers 3 types, 600x600, 300x1200, and 600x1200mm with max: 140lm/w. Its UGR19 brings more visual comfort in the office. Equipped with Dali, Interact and EcoSet, RC099V G2 offers easy connection to control system to bring better energy saving.

Product data

General Information		Number of products on MCB of 16 A type B 17	
Light source engine type	LED	Protection class IEC	Safety class II
Service tag	Yes		
Value ladder	Performance	Controls and Dimming	
		Dimmable	No
		Control interface	-
Light Technical		Mechanical and Housing	
Luminous Flux	3,600 lm	Housing Material	Metal
Correlated Color Temperature (Nom)	4000 K	Optical cover material	Polystyrene
Luminous Efficacy (rated) (Nom)	110 lm/W	Housing Color	White RAL 9003
Color rendering index (CRI)	>80	Optical cover finish	Opal
Light source color	840 neutral white	Ingress protection code	IP20 [Finger-protected]
		Mech. impact protection code	IK03 [0.3 J]
Operating and Electrical		Optical cover type	Opal
Input Voltage	220-240 V	Net Weight (Piece)	1.800 kg
Line Frequency	50 or 60 Hz		
Power Consumption	32.7 W		
Power Factor (Fraction)	0.9		

GreenPerform Panel RC099V G3

Approval and Application

CE mark	Yes
Ambient temperature range	-20 °C to 45 °C

Initial Performance (IEC Compliant)

Luminous flux tolerance	-10% / +10%
Power consumption tolerance	+/-10%

Product Data

Order product name	RC099V G3 LED37/840 PSU W60L60 OC
--------------------	-----------------------------------

Full product name	RC099V G3 LED37/840 PSU W60L60 OC
Full product code	692382867198399
Order code	911401585942
Material Nr. (12NC)	911401585942
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	6923828671983
Numerator - Packs per outer box	4
EAN/UPC - Case	6923828671983

