



GreenUp Linear

SM308C P45/865 L170W3 PSU WB WH

GreenUp Linear, 45 W, 4410 lm, 6500 K, Frosted, IP20 | Finger-protected

Retail & Hospitality has a clear trend that clusters of choices is one of the most important DNAs that being strongly expected in this specific applications. GreenUp Linear is the entry level linear product family, which offers the basic functional lighting performance, with multiple choices of installations, lumen outputs and product dimensions.

Product data

General Information		Protection class IEC	
Light source engine type	LED	Safety class II	
Value ladder	Value	Controls and Dimming	
Light Technical		Dimmable	No
Luminous Flux	4,410 lm	Control interface	-
Correlated Color Temperature (Nom)	6500 K	Mechanical and Housing	
Luminous Efficacy (rated) (Nom)	98 lm/W	Housing Material	Aluminum extruded
Color rendering index (CRI)	>80	Optical cover material	Polycarbonate
Light source color	865 cool daylight	Housing Color	White RAL 9003
Operating and Electrical		Optical cover finish	Frosted
Input Voltage	220-240 V	Ingress protection code	IP20 [Finger-protected]
Line Frequency	50 or 60 Hz	Mech. impact protection code	IK03 [0.3 J]
Power Consumption	45 W	Optical cover type	Polycarbonate Diffuser
Power Factor (Fraction)	0.9	Net Weight (Piece)	1.760 kg
Number of products on MCB of 16 A type B	45	Approval and Application	
		CE mark	No

GreenUp Linear

Ambient temperature range	+20 to +40 °C
Initial Performance (IEC Compliant)	
Luminous flux tolerance	+/-10%
Power consumption tolerance	+/-10%
Product Data	
Order product name	SM308C P45/865 L170W3 PSU WB WH
Full product name	SM308C P45/865 L170W3 PSU WB WH

Full product code	872016952872799
Order code	911401586322
Material Nr. (12NC)	911401586322
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8720169528727
Numerator - Packs per outer box	4
EAN/UPC - Case	8720169540217

Dimensional drawing

