



Flex Cove G6

LS168S LED12 940 IP20 L5000 COB

Flex Cove G6, 1350 lm, 95 lm/W, 940 neutral white, 24 DC V, IP20 | Finger-protected

Philips Flex Cove G6 is the latest generation of our popular LED cove lighting. This comprehensive new family of flexible strip lights are designed to follow straight lines or curves to create beautiful ambiances that highlight architectural details. Both SPEC fighter and COST fighter are available within the family. As customizable cove lighting strips, SPEC fighter range also promise excellent energy-saving performance, superb lighting uniformity, and color consistency. All with a long lifetime that promises less lumen decay or color shifts. So with Flex Cove G6, you can flex your accent lighting to suit the requirements of any project - beautifully.

Product data

General Information		Optic type	
Number of gear units	-	Optic type	-
Gear	-	Luminaire light beam spread	-
Driver included	No	Unified glare rating CEN	Not applicable
Light source engine type	LED	Operating and Electrical	
Warranty period	3 years	Input Voltage	24 DC V
		Line Frequency	- Hz
		Power Consumption	53.55 W
		Power Factor (Fraction)	-
		Connection	-
		Cable	-
		Number of products on MCB of 16 A type B	-
		Suitable for random switching	No
		Protection class IEC	Safety class III
Light Technical			
Luminous Flux	1,350 lm		
Correlated Color Temperature (Nom)	4000 K		
Luminous Efficacy (rated) (Nom)	95 lm/W		
Color rendering index (CRI)	90		
Number of light sources	512		
Beam angle of light source	140 degree(s)		
Light source color	940 neutral white		

Flex Cove G6

Controls and Dimming

Dimmable	1-10V DALI Fixed
Control interface	-
Maximum dim level	Not applicable

Mechanical and Housing

Housing Material	Polycarbonate
Reflector material	-
Optic material	-
Optical cover material	-
Housing Color	-
Mounting device	-
Optical cover finish	-
Overall length	5,000 mm
Overall width	8 mm
Overall height	1.8 mm
Dimensions (Height x Width x Depth)	2 x 8 x 5000 mm
Ingress protection code	IP20 [Finger-protected]
Mech. impact protection code	-
Optical cover type	-
Net Weight (Piece)	0.070 kg

Approval and Application

Glow-wire test	-
Flammability mark	-

CE mark	No
ENEC mark	-
Photobiological risk	Photobiological risk group 0 @200mm to EN62778
EU RoHS compliant	Yes
Performance ambient temperature Tq	25 °C
Ambient temperature range	-20 to +45 °C

Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-10%
Initial chromaticity	(0.380,0.380) SDCM<5
Power consumption tolerance	+/-10%

Product Data

Order product name	LS168S LED12 940 IP20 L5000 COB
Full product name	LS168S LED12 940 IP20 L5000 COB
Full product code	692382863585599
Order code	911401586746
Material Nr. (12NC)	911401586746
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	6923828635855
Numerator - Packs per outer box	100
EAN/UPC - Case	6923828636814

Dimensional drawing

