



GreenUp Linear

SP308P P45/840 L170W3 PSU MB WH

GreenUp Linear, 98 lm/W, 840 neutral white

Retail & Hospitality has a clear trend that clusters of choices is one of the most important DNAs that being strongly expected in this specific applications. GreenUp Linear is the entry level linear product family, which offers the basic functional lighting performance, with multiple choices of installations, lumen outputs and product dimensions.

Product data

General Information	
Light source engine type	LED
Value ladder	Value

Light Technical	
Luminous Flux	4,410 lm
Correlated Color Temperature (Nom)	4000 K
Luminous Efficacy (rated) (Nom)	98 lm/W
Color rendering index (CRI)	>80
Light source color	840 neutral white

Operating and Electrical	
Input Voltage	220-240 V
Line Frequency	50 or 60 Hz
Power Consumption	45 W
Power Factor (Fraction)	0.9
Number of products on MCB of 16 A type B	45
Protection class IEC	Safety class II

Controls and Dimming	
Dimmable	No
Control interface	-

Mechanical and Housing	
Housing Material	Aluminum extruded
Optical cover material	Polycarbonate
Housing Color	White RAL 9003
Optical cover finish	Frosted
Ingress protection code	IP20 [Finger-protected]
Mech. impact protection code	IK03 [0.3 J]
Optical cover type	Polycarbonate Diffuser
Net Weight (Piece)	1.760 kg

Approval and Application	
CE mark	No
Ambient temperature range	+20 to +40 °C

Initial Performance (IEC Compliant)	
Luminous flux tolerance	+/-10%

Power consumption tolerance	+/-10%
Product Data	
Order product name	SP308P P45/840 L170W3 PSU MB WH
Full product name	SP308P P45/840 L170W3 PSU MB WH
Full product code	872016953167399
Order code	53167399

Material Nr. (12NC)	911401588422
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8720169531673
Numerator - Packs per outer box	4
EAN/UPC - Case	8720169543164

Dimensional drawing

