



# GreenSpace Surface Mount

## SM303C P9S 950 PSU MB

GreenSpace Surface Mount, 8.1 W, 9.9 W, 780 lm, 5000 K, Frosted, IP20 | Finger-protected

Retail & Hospitality has a clear trend that clusters of choices is one of the most important DNAs that being strongly expected in this specific applications. GreenSpace Surface Mount is the entry level downlight family dedicated with suspension and surface mount versions, which offers a complete range of options for optical solutions, lumen outputs and color temperatures with multiple form factors available.

### Product data

General Information	
Light source engine type	LED
Value ladder	Performance

  

Light Technical	
Luminous Flux	780 lm
Correlated Color Temperature (Nom)	5000 K
Luminous Efficacy (rated) (Nom)	87 lm/W
Color rendering index (CRI)	>90
Light source color	White

  

Operating and Electrical	
Input Voltage	200 to 240 V
Line Frequency	50 to 60 Hz
Power Consumption	8.1 9.9 W

  

Power Factor (Fraction)	0.5
Number of products on MCB of 16 A type B	-
Protection class IEC	Safety class II

  

Controls and Dimming	
Dimmable	No
Control interface	-

  

Mechanical and Housing	
Housing Material	Aluminum Alloy
Optical cover material	Acrylate
Housing Color	White
Optical cover finish	Frosted
Ingress protection code	IP20 [Finger-protected]
Mech. impact protection code	IK03 [0.3 J]

## GreenSpace Surface Mount

Optical cover type	Acrylate
Net Weight (Piece)	0.391 kg

### Approval and Application

CE mark	No
Ambient temperature range	-20 to +40 °C

### Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-10%
Power consumption tolerance	+/-10%

### Product Data

Order product name	SM303C P9S 950 PSU MB
--------------------	-----------------------

Full product name	SM303C P9S 950 PSU MB
Full product code	872016952614399
Order code	911401588512
Material Nr. (12NC)	911401588512
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8720169526143
Numerator - Packs per outer box	24
EAN/UPC - Case	8720169537637

## Dimensional drawing

