



ModiFly suspended

SP800P LED21/840 L60W6 CD

ModiFly suspended, 120 lm/W, 840 neutral white

ModiFly is the new action hero for lighting design. This next generation lighting innovation has it all: contemporary form, infinite design freedom, and undisputed performance. Simple, yet sophisticated, ModiFly has a style that lends itself perfectly for a variety of spaces including open offices, education, and retail environments, where visual comfort and design continuity are essential.

Product data

General Information	
Light source engine type	LED
Service tag	Yes
Value ladder	Specification
Light Technical	
Luminous Flux	2,100 lm
Correlated Color Temperature (Nom)	4000 K
Luminous Efficacy (rated) (Nom)	120 lm/W
Color rendering index (CRI)	≥80
Light source color	840 neutral white
Effective projected area	0.039438 m²
Operating and Electrical	
Input Voltage	220 to 240 V
Line Frequency	50 or 60 Hz
Inrush current	14.1 A
Power Consumption	17.5 W
Power Factor (Fraction)	0.9
Number of products on MCB of 16 A type B	35

Protection class IEC	Safety class I
Controls and Dimming	
Dimmable	No
Control interface	-
Mechanical and Housing	
Housing Material	Aluminium
Optical cover material	Polymethyl methacrylate
Housing Color	Aluminum and white
Optical cover finish	Frosted
Overall length	626 mm
Overall width	63 mm
Overall height	105 mm
Dimensions (Height x Width x Depth)	105 x 63 x 626 mm
Ingress protection code	IP20 [Finger-protected]
Mech. impact protection code	IK03 [0.3 J]
Optical cover type	Polymethyl methacrylate bowl/cover
Net Weight (Piece)	2.580 kg

ModiFly suspended

Approval and Application	
Flammability mark	-
CE mark	Yes
Ambient temperature range	-20 to +40 °C
Initial Performance (IEC Compliant)	
Luminous flux tolerance	+/-10%
Initial chromaticity	0.3818,0.3796
Power consumption tolerance	+/-10%
Product Data	
Order product name	SP800P LED21/840 L60W6 CD

Full product name	SP800P LED21/840 L60W6 CD
Full product code	872016972962900
Order code	911401589332
Material Nr. (12NC)	911401589332
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8720169729629
Numerator - Packs per outer box	1
EAN/UPC - Case	8720169729629

