



ModiFly suspended

SP800P LED21/840 L60W6 SD

ModiFly suspended, 120 lm/W, 840 neutral white

ModiFly is the new action hero for lighting design. This next generation lighting innovation has it all: contemporary form, infinite design freedom, and undisputed performance. Simple, yet sophisticated, ModiFly has a style that lends itself perfectly for a variety of spaces including open offices, education, and retail environments, where visual comfort and design continuity are essential.

Product data

| General Information | |
|--------------------------|---------------|
| Light source engine type | LED |
| Service tag | Yes |
| Value ladder | Specification |

| Light Technical | |
|------------------------------------|-------------------------|
| Luminous Flux | 2,100 lm |
| Correlated Color Temperature (Nom) | 4000 K |
| Luminous Efficacy (rated) (Nom) | 120 lm/W |
| Color rendering index (CRI) | ≥80 |
| Light source color | 840 neutral white |
| Effective projected area | 0.039438 m ² |

| Operating and Electrical | |
|--|--------------|
| Input Voltage | 220 to 240 V |
| Line Frequency | 50 or 60 Hz |
| Inrush current | 14.1 A |
| Power Consumption | 17.5 W |
| Power Factor (Fraction) | 0.9 |
| Number of products on MCB of 16 A type B | 35 |

| | |
|----------------------|----------------|
| Protection class IEC | Safety class I |
|----------------------|----------------|

| Controls and Dimming | |
|----------------------|----|
| Dimmable | No |
| Control interface | - |

| Mechanical and Housing | |
|-------------------------------------|------------------------------------|
| Housing Material | Aluminium |
| Optical cover material | Polymethyl methacrylate |
| Housing Color | Aluminum and white |
| Optical cover finish | Frosted |
| Overall length | 626 mm |
| Overall width | 63 mm |
| Overall height | 105 mm |
| Dimensions (Height x Width x Depth) | 105 x 63 x 626 mm |
| Ingress protection code | IP20 [Finger-protected] |
| Mech. impact protection code | IK03 [0.3 J] |
| Optical cover type | Polymethyl methacrylate bowl/cover |
| Net Weight (Piece) | 2.620 kg |

ModiFly suspended

Approval and Application

| | |
|---------------------------|---------------|
| Flammability mark | - |
| CE mark | Yes |
| Ambient temperature range | -20 to +40 °C |

Initial Performance (IEC Compliant)

| | |
|-----------------------------|---------------|
| Luminous flux tolerance | +/-10% |
| Initial chromaticity | 0.3818,0.3796 |
| Power consumption tolerance | +/-10% |

Product Data

| | |
|--------------------|---------------------------|
| Order product name | SP800P LED21/840 L60W6 SD |
|--------------------|---------------------------|

| | |
|---------------------------------|---------------------------|
| Full product name | SP800P LED21/840 L60W6 SD |
| Full product code | 872016972960500 |
| Order code | 911401590332 |
| Material Nr. (12NC) | 911401590332 |
| Numerator - Quantity Per Pack | 1 |
| EAN/UPC - Product/Case | 8720169729605 |
| Numerator - Packs per outer box | 1 |
| EAN/UPC - Case | 8720169729605 |

