



# GreenUp Linear Flex

## SP309P P55UD/840 L120W5 PSU HD 2 BK

GreenUp Linear Flex, 90 lm/W, 840 neutral white

Retail & Hospitality has a clear trend that clusters of choices is one of the most important DNAs that being strongly expected in this specific applications. GreenUp Linear Flex is a comprehensive product family which offers a variety of combinations between decorative and functional lighting units. It supports every of your desires with flexible linear family including suspension and recessed installations.

### Product data

General Information	
Light source engine type	LED
Value ladder	Value
Light Technical	
Luminous Flux	4,950 lm
Correlated Color Temperature (Nom)	4000 K
Luminous Efficacy (rated) (Nom)	90 lm/W
Color rendering index (CRI)	>80
Light source color	840 neutral white
Operating and Electrical	
Input Voltage	220-240 V
Line Frequency	50 or 60 Hz
Power Consumption	55 W
Power Factor (Fraction)	0.9
Number of products on MCB of 16 A type B	37
Protection class IEC	Safety class II

Controls and Dimming	
Dimmable	No
Control interface	-
Mechanical and Housing	
Housing Material	Aluminum extruded
Optical cover material	Polycarbonate
Housing Color	Black
Optical cover finish	Frosted
Ingress protection code	IP20 [Finger-protected]
Mech. impact protection code	IK03 [0.3 J]
Optical cover type	Linear-lens array oval shape
Net Weight (Piece)	2.790 kg

Approval and Application	
CE mark	No
Ambient temperature range	-20 to +40 °C

Initial Performance (IEC Compliant)	
Luminous flux tolerance	+/-10%

## GreenUp Linear Flex

Power consumption tolerance	+/-10%
<b>Product Data</b>	
Order product name	SP309P P55UD/840 L120W5 PSU HD 2 BK
Full product name	SP309P P55UD/840 L120W5 PSU HD 2 BK
Full product code	872016953046199
Order code	911401590422

Material Nr. (12NC)	911401590422
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8720169530461
Numerator - Packs per outer box	3
EAN/UPC - Case	8720169541955

### Dimensional drawing

