



GreenSpace Surface Mount

SP303P P6 940 PSU VWB

GreenSpace Surface Mount, 91 lm/W, 940 neutral white

Retail & Hospitality has a clear trend that clusters of choices is one of the most important DNAs that being strongly expected in this specific applications. GreenSpace Surface Mount is the entry level downlight family dedicated with suspension and surface mount versions, which offers a complete range of options for optical solutions, lumen outputs and color temperatures with multiple form factors available.

Product data

| General Information | | Number of products on MCB of 16 A type B | |
|------------------------------------|-------------------|--|-------------------------|
| Light source engine type | LED | | - |
| Value ladder | Performance | Protection class IEC | Safety class II |
| Light Technical | | Controls and Dimming | |
| Luminous Flux | 550 lm | Dimmable | No |
| Correlated Color Temperature (Nom) | 4000 K | Control interface | - |
| Luminous Efficacy (rated) (Nom) | 91 lm/W | Mechanical and Housing | |
| Color rendering index (CRI) | >90 | Housing Material | Aluminum Alloy |
| Light source color | 940 neutral white | Optical cover material | Acrylate |
| Operating and Electrical | | Housing Color | White |
| Input Voltage | 200 to 240 V | Optical cover finish | Frosted |
| Line Frequency | 50 to 60 Hz | Ingress protection code | IP20 [Finger-protected] |
| Power Consumption | 5.4 6.6 W | Mech. impact protection code | IK03 [0.3 J] |
| Power Factor (Fraction) | 0.5 | Optical cover type | Acrylate |

GreenSpace Surface Mount

| | |
|--------------------|----------|
| Net Weight (Piece) | 0.805 kg |
|--------------------|----------|

Approval and Application

| | |
|---------------------------|---------------|
| CE mark | No |
| Ambient temperature range | -20 to +40 °C |

Initial Performance (IEC Compliant)

| | |
|-----------------------------|--------|
| Luminous flux tolerance | +/-10% |
| Power consumption tolerance | +/-10% |

Product Data

| | |
|--------------------|-----------------------|
| Order product name | SP303P P6 940 PSU VWB |
|--------------------|-----------------------|

| | |
|---------------------------------|-----------------------|
| Full product name | SP303P P6 940 PSU VWB |
| Full product code | 872016952896399 |
| Order code | 52896399 |
| Material Nr. (12NC) | 911401592312 |
| Numerator - Quantity Per Pack | 1 |
| EAN/UPC - Product/Case | 8720169528963 |
| Numerator - Packs per outer box | 12 |
| EAN/UPC - Case | 8720169540453 |

Dimensional drawing

