



# GreenSpace Surface Mount

## SP303P P6 950 PSU NB

GreenSpace Surface Mount, 81 lm/W, White

Retail & Hospitality has a clear trend that clusters of choices is one of the most important DNAs that being strongly expected in this specific applications. GreenSpace Surface Mount is the entry level downlight family dedicated with suspension and surface mount versions, which offers a complete range of options for optical solutions, lumen outputs and color temperatures with multiple form factors available.

### Product data

General Information	
Light source engine type	LED
Value ladder	Performance

  

Light Technical	
Luminous Flux	490 lm
Correlated Color Temperature (Nom)	5000 K
Luminous Efficacy (rated) (Nom)	81 lm/W
Color rendering index (CRI)	>90
Light source color	White

  

Operating and Electrical	
Input Voltage	200 to 240 V
Line Frequency	50 to 60 Hz
Power Consumption	5.4 6.6 W
Power Factor (Fraction)	0.5

  

Number of products on MCB of 16 A type B	-
Protection class IEC	Safety class II

  

Controls and Dimming	
Dimmable	No
Control interface	-

  

Mechanical and Housing	
Housing Material	Aluminum Alloy
Optical cover material	Acrylate
Housing Color	White
Optical cover finish	Frosted
Ingress protection code	IP20 [Finger-protected]
Mech. impact protection code	IK03 [0.3 J]
Optical cover type	Acrylate

## GreenSpace Surface Mount

Net Weight (Piece)	0.805 kg
--------------------	----------

### Approval and Application

CE mark	No
Ambient temperature range	-20 to +40 °C

### Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-10%
Power consumption tolerance	+/-10%

### Product Data

Order product name	SP303P P6 950 PSU NB
--------------------	----------------------

Full product name	SP303P P6 950 PSU NB
Full product code	872016952373999
Order code	52373999
Material Nr. (12NC)	911401592412
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8720169523739
Numerator - Packs per outer box	12
EAN/UPC - Case	8720169535220

## Dimensional drawing

