



CoreView G4 RC420B

RC420V G4 LED38/850 W60L60 PSU

CoreView G4 RC420B, 106 lm/W, 850 neutral white

RC420B G4 inherits the elegant and classic indirect light design from previous generation but with slimmer outlook. It offers 3 types, 600x600, 300x1200, and 600x1200 (Customized offer)mm with max: 108lm/w. Air slot option applies to 600x1200mm type to give fast and easy support to the projects where air outlet is required from the office lighting fittings. Full indirect light design provides visual comfort in the office area as well.

Product data

General Information		Protection class IEC	
Color Code	850 neutral white	Safety class II	
Light source engine type	LED	Controls and Dimming	
Service tag	Yes	Dimmable	No
Value ladder	Performance	Control interface	-
Light Technical		Mechanical and Housing	
Luminous Flux	3,800 lm	Housing Material	Steel
Correlated Color Temperature (Nom)	5000 K	Optical cover material	Polycarbonate
Luminous Efficacy (rated) (Nom)	106 lm/W	Housing Color	White RAL 9003
Color rendering index (CRI)	>80	Optical cover finish	Frosted
Light source color	850 neutral white	Ingress protection code	IP20 [Finger-protected]
Operating and Electrical		Mech. impact protection code	-
Input Voltage	220 to 240 V	Optical cover type	-
Line Frequency	50 or 60 Hz	Net Weight (Piece)	3,340 kg
Power Consumption	36 W	Approval and Application	
Power Factor (Fraction)	0.9	CE mark	Yes
Number of products on MCB of 16 A type B	40		

CoreView G4 RC420B

Ambient temperature range	-20 to +45 °C
---------------------------	---------------

Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-10%
Power consumption tolerance	+/-10%

Product Data

Order product name	RC420V G4 LED38/850 W60L60 PSU
--------------------	--------------------------------

Full product name	RC420V G4 LED38/850 W60L60 PSU
-------------------	--------------------------------

Order code	911401594371
------------	--------------

Material Nr. (12NC)	911401594371
---------------------	--------------

Numerator - Quantity Per Pack	1
-------------------------------	---

Numerator - Packs per outer box	2
---------------------------------	---

Dimensional drawing

