



# GreenPerform Panel RC099V G3

## RC099V G3 LED56/840 PSD W60L120

GreenPerform Panel RC099V G3, 125 lm/W, 840 neutral white, DALI

GreenPerform panel RC099V G3 is an affordable LED panel delivering comfortable light with excellent uniformity. It offers 3 types, 600x600,300x1200, and 600x1200mm with max: 140lm/w. Its UGR19 brings more visual comfort in the office. Equipped with Dali, Interact and EcoSet, RC099V G2 offers easy connection to control system to bring better energy saving.

### Product data

General Information		Power Factor (Fraction)		0.9
Light source engine type	LED	Number of products on MCB of 16 A type B	17	
Service tag	Yes	Protection class IEC	Safety class II	
Value ladder	Performance	<b>Controls and Dimming</b>		
<b>Light Technical</b>		Dimmable	DALI	
Luminous Flux	5,400 lm	Control interface	DALI	
Correlated Color Temperature (Nom)	4000 K	<b>Mechanical and Housing</b>		
Luminous Efficacy (rated) (Nom)	125 lm/W	Housing Material	Metal	
Color rendering index (CRI)	>80	Optical cover material	Polystyrene	
Light source color	840 neutral white	Housing Color	White RAL 9003	
<b>Operating and Electrical</b>		Optical cover finish	Opal	
Input Voltage	220-240 V	Ingress protection code	IP20 [Finger-protected]	
Line Frequency	50 or 60 Hz	Mech. impact protection code	IK03 [0.3 J]	
Power Consumption	43.2 W	Optical cover type	Opal	

# GreenPerform Panel RC099V G3

Net Weight (Piece)	3.400 kg
<b>Approval and Application</b>	
CE mark	Yes
Ambient temperature range	-20 °C to 45 °C
<b>Initial Performance (IEC Compliant)</b>	
Luminous flux tolerance	-10% / +10%
Power consumption tolerance	+/-10%

<b>Product Data</b>	
Order product name	RC099V G3 LED56/840 PSD W60L120
Full product name	RC099V G3 LED56/840 PSD W60L120
Order code	911401594542
Material Nr. (12NC)	911401594542
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	2

