GreenPerform Canopy Mini500 G4

BBP500 G4 LED180/NW PSU S-MB

GreenPerform Canopy Mini500 G4, 122 W, 18066 lm, 4000 K

The Philips GreenPerform Canopy Mini500 Gen4 lives up to the GreenPerform family's enviable reputation for reliable performance. Not only does this next-generation, energy-saving LED deliver leading system efficacy and extended long-term quality, it also offers a versatile selection of optics, connectivity, controls and installation options. So you can create the ideal lighting conditions for any space, at any time. The GreenPerform Canopy portfolio also includes a series that is ideal for canopy lighting in food applications. For professionals who demand high-performance, connected lighting for their lighting installations, this robust, optimized, and versatile family of LED canopy luminaires is the perfect choice for both indoor and outdoor canopy applications.

Product data

General Information	
Light source engine type	LED
Service tag	Yes
Value ladder	Performance

Light Technical	
Luminous Flux	18,066 lm
Correlated Color Temperature (Nom)	4000 K
Luminous Efficacy (rated) (Nom)	148 lm/W
Color rendering index (CRI)	>80
Light source color	840 neutral white

Operating and Electrical	
Input Voltage	220-240 V
Line Frequency	50 to 60 Hz
Inrush current	35.4 A
Power Consumption	122 W
Power Factor (Fraction)	0.95
Number of products on MCB of 16 A type B	8
Protection class IEC	Safety class I

Controls and Dimming	
Dimmable	No

GreenPerform Canopy Mini500 G4

Control interface	-

Mechanical and Housing

Housing Material	Aluminium die-cast ADC1 - alloy grade (EN AC-47100)
Optical cover material	Tempered glass
Housing Color	White
Optical cover finish	Clear
Overall length	423 mm
Overall width	400 mm
Overall height	96 mm
Dimensions (Height x Width x Depth)	96 x 400 x 423 mm
Ingress protection code	IP65 [Dust penetration-protected, jet-proof]
Mech. impact protection code	IK07 [2 J reinforced]
Optical cover type	Clear glass
Net Weight (Piece)	4.790 kg

Approval and Application

Flammability mark	For mounting on normally flammable surfaces
CE mark	Yes
Ambient temperature range	-40 to +45 °C

Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-10%
Power consumption tolerance	+/-10%

Product Data

Order product name	BBP500 G4 LED180/NW PSU S-MB
Full product name	BBP500 G4 LED180/NW PSU S-MB
Full product code	872016954799500
Order code	911401595032
Material Nr. (12NC)	911401595032
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8720169547995
Numerator - Packs per outer box	1
EAN/UPC - Case	8720169547995

Dimensional drawing



© 2025 Signify Holding All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.