



CoreView G4 RC420B

RC420V G4 LED38/840 W30L120 PSD

CoreView G4 RC420B, 111 lm/W, 840 neutral white, DALI

RC420B G4 inherits the elegant and classic indirect light design from previous generation but with slimmer outlook. It offers 3 types, 600x600, 300x1200, and 600x1200 (Customized offer)mm with max: 108lm/w. Air slot option applies to 600x1200mm type to give fast and easy support to the projects where air outlet is required from the office lighting fittings. Full indirect light design provides visual comfort in the office area as well.

Product data

General Information		Protection class IEC	
Color Code	840 neutral white		Safety class II
Light source engine type	LED	Controls and Dimming	
Service tag	Yes	Dimmable	Yes
Value ladder	Performance	Control interface	DALI
Light Technical		Mechanical and Housing	
Luminous Flux	4,000 lm	Housing Material	Steel
Correlated Color Temperature (Nom)	4000 K	Optical cover material	-
Luminous Efficacy (rated) (Nom)	111 lm/W	Housing Color	White RAL 9003
Color rendering index (CRI)	>80	Optical cover finish	-
Light source color	840 neutral white	Ingress protection code	IP20 [Finger-protected]
Operating and Electrical		Mech. impact protection code	-
Input Voltage	220 to 240 V	Optical cover type	-
Line Frequency	50 or 60 Hz	Net Weight (Piece)	3.660 kg
Power Consumption	36 W	Approval and Application	
Power Factor (Fraction)	0.9	CE mark	Yes
Number of products on MCB of 16 A type B	24		

CoreView G4 RC420B

Ambient temperature range	-20 to +45 °C
---------------------------	---------------

Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-10%
Power consumption tolerance	+/-10%

Product Data

Order product name	RC420V G4 LED38/840 W30L120 PSD
--------------------	---------------------------------

Full product name	RC420V G4 LED38/840 W30L120 PSD
-------------------	---------------------------------

Order code	911401595671
------------	--------------

Material Nr. (12NC)	911401595671
---------------------	--------------

Numerator - Quantity Per Pack	1
-------------------------------	---

Numerator - Packs per outer box	2
---------------------------------	---

Dimensional drawing

