



CoreView G4 RC420B

RC420V G4 LED38/9TW W60L60

CoreView G4 RC420B, 84 lm/W, Tunable white, DALI

RC420B G4 inherits the elegant and classic indirect light design from previous generation but with slimmer outlook. It offers 3 types, 600x600, 300x1200, and 600x1200 (Customized offer)mm with max: 108lm/w. Air slot option applies to 600x1200mm type to give fast and easy support to the projects where air outlet is required from the office lighting fittings. Full indirect light design provides visual comfort in the office area as well.

Product data

General Information	
Color Code	Tunable white
Light source engine type	LED
Service tag	Yes
Value ladder	Performance
Light Technical	
Luminous Flux	3,290 lm
Correlated Color Temperature (Nom)	3000 - 6500 K
Luminous Efficacy (rated) (Nom)	84 lm/W
Color rendering index (CRI)	>80
Light source color	Tunable white
Operating and Electrical	
Input Voltage	220 to 240 V
Line Frequency	50 or 60 Hz
Power Consumption	39 W
Power Factor (Fraction)	0.9
Number of products on MCB of 16 A type B	24

Protection class IEC		Safety class I
Controls and Dimming		
Dimmable	Yes	
Control interface	DALI	
Mechanical and Housing		
Housing Material	Steel	
Optical cover material	Polycarbonate	
Housing Color	White RAL 9003	
Optical cover finish	Frosted	
Ingress protection code	IP20 [Finger-protected]	
Mech. impact protection code	-	
Optical cover type	-	
Net Weight (Piece)	4.340 kg	
Approval and Application		
CE mark	Yes	

CoreView G4 RC420B

Ambient temperature range	-20 to +45 °C
---------------------------	---------------

Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-10%
Power consumption tolerance	+/-10%

Product Data

Order product name	RC420V G4 LED38/9TW W60L60
--------------------	----------------------------

Full product name	RC420V G4 LED38/9TW W60L60
Order code	911401597571
Material Nr. (12NC)	911401597571
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	2

Dimensional drawing

