



# CoreView G4 RC420B

## RC420V G4 LED38/9TW W60L60

CoreView G4 RC420B, 84 lm/W, Tunable white, DALI

RC420B G4 inherits the elegant and classic indirect light design from previous generation but with slimmer outlook. It offers 3 types, 600x600, 300x1200, and 600x1200 (Customized offer)mm with max: 108lm/w. Air slot option applies to 600x1200mm type to give fast and easy support to the projects where air outlet is required from the office lighting fittings. Full indirect light design provides visual comfort in the office area as well.

### Product data

General Information		Protection class IEC	
Color Code	Tunable white	Safety class I	
Light source engine type	LED	Controls and Dimming	
Service tag	Yes	Dimmable	Yes
Value ladder	Performance	Control interface	DALI
Light Technical		Mechanical and Housing	
Luminous Flux	3,290 lm	Housing Material	Steel
Correlated Color Temperature (Nom)	3000 - 6500 K	Optical cover material	Polycarbonate
Luminous Efficacy (rated) (Nom)	84 lm/W	Housing Color	White RAL 9003
Color rendering index (CRI)	>80	Optical cover finish	Frosted
Light source color	Tunable white	Ingress protection code	IP20 [Finger-protected]
		Mech. impact protection code	-
Operating and Electrical		Optical cover type	-
Input Voltage	220 to 240 V	Net Weight (Piece)	4.340 kg
Line Frequency	50 or 60 Hz	Approval and Application	
Power Consumption	39 W	CE mark	Yes
Power Factor (Fraction)	0.9		
Number of products on MCB of 16 A type B	24		

# CoreView G4 RC420B

Ambient temperature range	-20 to +45 °C
---------------------------	---------------

## Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-10%
Power consumption tolerance	+/-10%

## Product Data

Order product name	RC420V G4 LED38/9TW W60L60
--------------------	----------------------------

Full product name	RC420V G4 LED38/9TW W60L60
-------------------	----------------------------

Order code	911401597571
------------	--------------

Material Nr. (12NC)	911401597571
---------------------	--------------

Numerator - Quantity Per Pack	1
-------------------------------	---

Numerator - Packs per outer box	2
---------------------------------	---

## Dimensional drawing

