



CoreView G4 RC420B

RC420V G4 LED38/9TW W60L60

CoreView G4 RC420B, 84 lm/W, Tunable white, DALI

RC420B G4 inherits the elegant and classic indirect light design from previous generation but with slimmer outlook. It offers 3 types, 600x600, 300x1200, and 600x1200 (Customized offer)mm with max: 108lm/w. Air slot option applies to 600x1200mm type to give fast and easy support to the projects where air outlet is required from the office lighting fittings. Full indirect light design provides visual comfort in the office area as well.

Product data

General Information		Protection class IEC		Safety class I	
Color Code	Tunable white				
Light source engine type	LED	Controls and Dimming			
Service tag	Yes	Dimmable	Yes		
Value ladder	Performance	Control interface	DALI		
Light Technical		Mechanical and Housing			
Luminous Flux	3,290 lm	Housing Material	Steel		
Correlated Color Temperature (Nom)	3000 - 6500 K	Optical cover material	Polycarbonate		
Luminous Efficacy (rated) (Nom)	84 lm/W	Housing Color	White RAL 9003		
Color rendering index (CRI)	>80	Optical cover finish	Frosted		
Light source color	Tunable white	Ingress protection code	IP20 [Finger-protected]		
		Mech. impact protection code	-		
Operating and Electrical		Optical cover type	-		
Input Voltage	220 to 240 V	Net Weight (Piece)	4.340 kg		
Line Frequency	50 or 60 Hz				
Power Consumption	39 W	Approval and Application			
Power Factor (Fraction)	0.9	CE mark	Yes		
Number of products on MCB of 16 A type B	24				

CoreView G4 RC420B

Ambient temperature range	-20 to +45 °C
---------------------------	---------------

Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-10%
Power consumption tolerance	+/-10%

Product Data

Order product name	RC420V G4 LED38/9TW W60L60
--------------------	----------------------------

Full product name	RC420V G4 LED38/9TW W60L60
Order code	911401597571
Material Nr. (12NC)	911401597571
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	2

Dimensional drawing

