



# GreenPerform Panel RC099V G3

## RC099V G3 LED50/840 PSD W60L120 OC HE

GreenPerform Panel RC099V G3, 135 lm/W, 840 neutral white, DALI

GreenPerform panel RC099V G3 is an affordable LED panel delivering comfortable light with excellent uniformity. It offers 3 types, 600x600, 300x1200, and 600x1200mm with max: 140lm/w. Its UGR19 brings more visual comfort in the office. Equipped with Dali, Interact and EcoSet, RC099V G2 offers easy connection to control system to bring better energy saving.

### Product data

General Information		Power Factor (Fraction)		0.9
Light source engine type	LED	Number of products on MCB of 16 A type B		17
Service tag	Yes	Protection class IEC		Safety class II
Value ladder	Performance	<b>Controls and Dimming</b>		
<b>Light Technical</b>		Dimmable	DALI	
Luminous Flux	5,000 lm	Control interface	DALI	
Correlated Color Temperature (Nom)	4000 K	<b>Mechanical and Housing</b>		
Luminous Efficacy (rated) (Nom)	135 lm/W	Housing Material	Metal	
Color rendering index (CRI)	>80	Optical cover material	Polystyrene	
Light source color	840 neutral white	Housing Color	White RAL 9003	
<b>Operating and Electrical</b>		Optical cover finish	Opal	
Input Voltage	220-240 V	Ingress protection code	IP20 [Finger-protected]	
Line Frequency	50 or 60 Hz	Mech. impact protection code	IK03 [0.3 J]	
Power Consumption	37 W	Optical cover type	Opal	

## GreenPerform Panel RC099V G3

Net Weight (Piece)	3.390 kg
--------------------	----------

### Approval and Application

CE mark	Yes
---------	-----

Ambient temperature range	-20 °C to 45 °C
---------------------------	-----------------

### Initial Performance (IEC Compliant)

Luminous flux tolerance	-10% / +10%
-------------------------	-------------

Power consumption tolerance	+/-10%
-----------------------------	--------

### Product Data

Order product name	RC099V G3 LED50/840 PSD W60L120 OC HE
--------------------	--

Full product name	RC099V G3 LED50/840 PSD W60L120 OC HE
-------------------	--

Order code	911401597942
------------	--------------

Material Nr. (12NC)	911401597942
---------------------	--------------

Numerator - Quantity Per Pack	1
-------------------------------	---

Numerator - Packs per outer box	2
---------------------------------	---

