



GreenPerform Panel RC099V G3

RC099V G3 LED38/840 PSD W60L60 HE

GreenPerform Panel RC099V G3, 140 lm/W, 840 neutral white, DALI

GreenPerform panel RC099V G3 is an affordable LED panel delivering comfortable light with excellent uniformity. It offers 3 types, 600x600, 300x1200, and 600x1200mm with max: 140lm/w. Its UGR19 brings more visual comfort in the office. Equipped with Dali, Interact and EcoSet, RC099V G2 offers easy connection to control system to bring better energy saving.

Product data

General Information		Power Factor (Fraction)		0.9
Light source engine type	LED	Number of products on MCB of 16 A type B	17	
Service tag	Yes	Protection class IEC	Safety class II	
Value ladder	Performance	Controls and Dimming		
Light Technical		Dimmable	DALI	
Luminous Flux	3,800 lm	Control interface	DALI	
Correlated Color Temperature (Nom)	4000 K	Mechanical and Housing		
Luminous Efficacy (rated) (Nom)	140 lm/W	Housing Material	Metal	
Color rendering index (CRI)	>80	Optical cover material	Polystyrene	
Light source color	840 neutral white	Housing Color	White RAL 9003	
Operating and Electrical		Optical cover finish	Opal	
Input Voltage	220-240 V	Ingress protection code	IP20 [Finger-protected]	
Line Frequency	50 or 60 Hz	Mech. impact protection code	IK03 [0.3 J]	
Power Consumption	27.1 W	Optical cover type	Opal	

GreenPerform Panel RC099V G3

Net Weight (Piece)	1.790 kg
Approval and Application	
CE mark	Yes
Ambient temperature range	-20 °C to 45 °C
Initial Performance (IEC Compliant)	
Luminous flux tolerance	-10% / +10%
Power consumption tolerance	+/-10%

Product Data	
Order product name	RC099V G3 LED38/840 PSD W60L60 HE
Full product name	RC099V G3 LED38/840 PSD W60L60 HE
Order code	911401598442
Material Nr. (12NC)	911401598442
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	4

