



# GreenSpace Flex Luna

## RS378B P8 940 PSU-E MB M43 PRO

GreenSpace Flex Luna, 8 W, 940 neutral white, IP20 | Finger-protected

Ever-changing yet dependable, the moon reflects the very essence of hospitality lighting, which is adaptable, elegant, and always in tune with its surroundings. GreenSpace Flex Luna is designed to evoke a unique sensation. Like the moon, Luna does not overpower but enhances its surroundings, casting a glow that feels both intimate and grand. It is not just a light. It is an intimate experience.

### Product data

| General Information                      |                   | Protection class IEC         |                          |
|--|-------------------|------------------------------|--------------------------|
| Light source engine type                 | LED               | Safety class II              |                          |
| Value ladder                             | Performance       | Controls and Dimming         |                          |
| <b>Light Technical</b>                   |                   | Dimmable                     | -                        |
| Luminous Flux                            | 725 lm            | Control interface            | -                        |
| Correlated Color Temperature (Nom)       | 4000 K            | Mechanical and Housing       |                          |
| Luminous Efficacy (rated) (Nom)          | 91 lm/W           | Housing Material             | Aluminum Alloy           |
| Color rendering index (CRI)              | 92                | Optical cover material       | Polycarbonate            |
| Light source color                       | 940 neutral white | Housing Color                | Black                    |
| Unified glare rating CEN                 | 16                | Optical cover finish         | Structured optic         |
| <b>Operating and Electrical</b>          |                   | Ingress protection code      | IP20 [Finger-protected]  |
| Input Voltage                            | 220 to 240 V      | Mech. impact protection code | IK03 [0.35 J reinforced] |
| Line Frequency                           | 50 or 60 Hz       | Optical cover type           | Lens                     |
| Power Consumption                        | 8 W               | Net Weight (Piece)           | 0.160 kg                 |
| Power Factor (Fraction)                  | 0.9               | Approval and Application     |                          |
| Number of products on MCB of 16 A type B | 75                | CE mark                      | Yes                      |

## GreenSpace Flex Luna

|                           |               |
|---------------------------|---------------|
| Ambient temperature range | -20 to +45 °C |
|---------------------------|---------------|

### Initial Performance (IEC Compliant)

|                             |             |
|-----------------------------|-------------|
| Luminous flux tolerance     | -10% / +10% |
| Power consumption tolerance | +/-10%      |

### Product Data

|                    |                                |
|--------------------|--------------------------------|
| Order product name | RS378B P8 940 PSU-E MB M43 PRO |
|--------------------|--------------------------------|

|                                 |                                |
|---------------------------------|--------------------------------|
| Full product name               | RS378B P8 940 PSU-E MB M43 PRO |
| Order code                      | 911401598645                   |
| Material Nr. (12NC)             | 911401598645                   |
| Numerator - Quantity Per Pack   | 1                              |
| Numerator - Packs per outer box | 48                             |

### Dimensional drawing

