



GreenSpace Surface Mount

SP303P P6S 927 PSU MB

GreenSpace Surface Mount, 84 lm/W, 927 warm white

Retail & Hospitality has a clear trend that clusters of choices is one of the most important DNAs that being strongly expected in this specific applications. GreenSpace Surface Mount is the entry level downlight family dedicated with suspension and surface mount versions, which offers a complete range of options for optical solutions, lumen outputs and color temperatures with multiple form factors available.

Product data

General Information		
Light source engine type	LED	
Value ladder	Performance	
Number of products on MCB of 16 A type B		-
Protection class IEC		Safety class II
Light Technical		
Luminous Flux	500 lm	
Correlated Color Temperature (Nom)	2700 K	
Luminous Efficacy (rated) (Nom)	84 lm/W	
Color rendering index (CRI)	>90	
Light source color	927 warm white	
Controls and Dimming		
Dimmable	No	
Control interface	-	
Mechanical and Housing		
Housing Material	Aluminum Alloy	
Optical cover material	Acrylate	
Housing Color	White	
Optical cover finish	Frosted	
Ingress protection code	IP20 [Finger-protected]	
Mech. impact protection code	IK03 [0.3 J]	
Optical cover type	Acrylate	
Operating and Electrical		
Input Voltage	200 to 240 V	
Line Frequency	50 to 60 Hz	
Power Consumption	5.4 6.6 W	
Power Factor (Fraction)	0.5	

GreenSpace Surface Mount

Net Weight (Piece)	0.895 kg
--------------------	----------

Approval and Application

CE mark	No
Ambient temperature range	-20 to +40 °C

Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-10%
Power consumption tolerance	+/-10%

Product Data

Order product name	SP303P P6S 927 PSU MB
--------------------	-----------------------

Full product name	SP303P P6S 927 PSU MB
Full product code	872016953068399
Order code	911401598912
Material Nr. (12NC)	911401598912
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8720169530683
Numerator - Packs per outer box	12
EAN/UPC - Case	8720169542174

Dimensional drawing

