



GreenVision All-in-one Solar Street Light

BRP715 LED70 CW Solar

Integrated solar street light with Lithium Ferro Phosphate battery, solar panel and MPPT charge controller built into the luminaire. Pressure die cast aluminium for sturdiness and long life. Specially designed pole mounting bracket allows different tilt angles, lateral and pole top mounting. Adjustable LED module for better distribution of light when required.

Product data

General Information	
Driver included	Yes
Warranty period	3 years
Light Technical	
Luminous Flux	7,000 lm
Correlated Color Temperature (Nom)	5700 K
Color rendering index (CRI)	>70
Operating and Electrical	
Battery type	Lithium Ferro Phosphate
Battery ampere hour	18 Ah
Battery voltage	12.8 V
Battery charging & discharging cycles	2000
Panel type	Mono crystalline
Panel voltage	18 V
Panel peak wattage	40 W
Charge controller type	MPPT
Cable	-

Grid connection type	Off grid
Controls and Dimming	
Dimmable	Yes
Configurability	Configurable
Control interface	IR remote
Solar dimming profile	Dimming along with microwave sensor
Mechanical and Housing	
Housing Color	Black
Overall length	750 mm
Overall width	366 mm
Overall height	133 mm
Dimensions (Height x Width x Depth)	133 x 366 x 750 mm
Battery location	Inbuilt
Ingress protection code	IP65 [Dust penetration-protected, jet-proof]
Optical cover type	Polycarbonate
Net Weight (Piece)	10.190 kg

GreenVision All-in-one Solar Street Light

Approval and Application

CE mark	Yes
EU RoHS compliant	Yes
Ambient temperature range	-10 °C to 55 °C

Over Time Performance (IEC Compliant)

Median useful life L70B50	50,000 hour(s)
---------------------------	----------------

Product Data

Order product name	BRP715 LED70 CW Solar
--------------------	-----------------------

Full product name	BRP715 LED70 CW Solar
Full product code	871951495412000
Order code	911401625608
Material Nr. (12NC)	911401625608
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8719514954120
Numerator - Packs per outer box	1
EAN/UPC - Case	8719514954120

Dimensional drawing

BRP715 LED70 CW Solar

